



EMS-A-C0 Cable Tie Mount, Black, UV PA6.6, Two-Part Epoxy, 0.98x0.98", PK100

EMS-A-C0

Panduit EMS-A-C0 Epoxy Applied Cable Tie Mounts provide a fast, strong, economical method to secure wire/cable to most surfaces and eliminate the need to drill holes. The mounts are affixed with user supplied EMA epoxy. For use in outdoor environments and with miniature, intermediate and standard cable ties. Made of Weather Resistant Nylon 6.6, are black in color and come in packages of 100.

Specifications

Product Type	Cable Tie Mount
Application	Epoxy Applied Mounts to Secure Wire/Cable to Most Surfaces
Color	Black
Environment	Indoor/Outdoor
Material	Nylon 6.6
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Mount Method	Adhesive
Overall Length (In.)	0.98
Overall Length (mm)	24.9
Overall Width (In.)	0.98
Overall Width (mm)	50.3
Overall Height (In.)	0.98
Overall Height (mm)	24.9
Resistance Properties	UV-Resistant, Weather-Resistant
Standards Met	RoHS Compliant
Static Load Capacity (kg)	4.5
Static Load Capacity (lb)	10
For Use With	Miniature, Intermediate, Standard Cross-Section Ties

Packaging Detail

UPC	07498358017
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0288
Std. Ctn. Qty.	1000
Std. Ctn. Volume (cf)	0.2879