



## Wall Mount Cabinet, 18RU, 30" Depth, Windowed Door, Black

PZWMC1830W

The PanZone® Wall Mount Cabinet with windowed door is 30 inches deep and includes hinged doors on the front and back for complete access to networking equipment to make moves, adds, and changes easy. The removable side panels allow for access to cable routing. The enclosure is engineered to allow proper climate control for use with various networking equipment. The 18 RU enclosure is rated to 300 pounds and is black.

### Specifications

Product Type	Wall Mount Cabinet
Material	Steel
Mount Method	Wall Mount
Maximum Load Capacity (kg)	136.1
Maximum Load Capacity (lb)	300.04
Number of Rack Units	18
Overall Width (In.)	25
Overall Width (mm)	635
Overall Depth (In.)	30
Overall Depth (mm)	762
Overall Height (In.)	34
Overall Height (mm)	863.6
Raised Floor Depth (In.)	30
Raised Floor Depth (mm)	762
Color	Black
Sub Brand	PanZone®
Standards Met	Accepts 19" EIA Rack Mount Panels and Equipment, RoHS Compliant

### Packaging Detail

UPC	61305661101
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	20.8354
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000