
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


| Material | High Conductivity Seamless Copper Tube | | | |
|--|--|--|--|--|
| Plating | Electro-Tin | | | |
| Wire Size | 250 kcmil | | | |
| Wire Type | Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric | | | |
| Wire Strip Length | 1-11/16 in. | | | |
| Stud Size | 1/2 in. | | | |
| UL Listed Wire Connector | Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts. | | | |
| UL Temperature Rating | 90° C | | | |
| C.S.A Certified Wire Connector | Yes | | | |
| Panduit Color Code on Barrel | YELLOW | | | |
| Panduit Die Index No. on Barrel | P62 | | | |
| Alternate Industry Die Index No. () on Barrel | (16) | | | |






LISTED Wire Connector







| | | | | | | | | CORP. TINLEY PARK, ILLINOIS |
|----|------|------|------|------------------|--------|-----|-----|---|
| | | | | | | | | LCB250-12WH-X Copper Lug - One-Hole, Long Barrel with Window, 45° Angle Tongue |
| 00 | 4/17 | JHNU | JHNU | DRAWING RELEASED | 019765 | RGB | RGB | |

REV DATE BY CHK DESCRIPTION ECN -R SUP SCALE N/A DRAWING NO / CAD FILE LCB250-12WH-CUST