THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

WIRE MAPPING



= WHITE/ORANGE (+TX)

= ORANGE (-TX)

= WHITE/GREEN (+RX)


= N/C = N/C

= GREEN (-RX)

7 = N/C

8 = N/C

D-CODE



= WHITE/ORANGE (+TX) = WHITE/GREEN (+RX)

3 = ORANGE (-TX)4 = GREEN(-RX)

NOTES:

1. PART NUMBER: ICD14T1NTL*M


2. DIMENSIONS IN PARENTHESES ARE

IN METRIC.

3. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.

4. CABLE MEETS CATEGORY 5E REQUIREMENTS.

5. PART AVAILABLE IN 1M, 2M, 3M, 5M, 10M, 15M, 20M LENGTH.



TWIST TIE-

ICD14T1NTL*M M12 MALE-RJ45 D-CODE, STRAIGHT, STP, TPE, TEAL

CUSTOMER DRAWING

ITEM REVISION NAME 00396ECI/00 DATASET FILE NAME 00396ECI_DC/00A

OMER								į į				IRD ANGLE ROJECTION		
CUST	00A	6/4/19	JB0	DAJP	EOS	INITIAL RELEASE	ECN-INI-0015	MATERIAL		N.	/ A		DRAWING NUMBER 00396ECI	-DC
A-SIZE	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	JB0	DATE 6/4	/19	DAJP	NONE	SHEET 1 OF 1	SIZE