


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
HC2L**2 (SEE NOTE 1)	78.74 IN ±.36 IN (2000.0mm ±9.1mm)	0.8 LB (363g)	0.12 LB/FT (1.8g/cm)
HC2L**6 (SEE NOTE 1)	72.00 IN ±.36 IN (1828.8mm ±9.1mm)	0.7 LB (318g)	0.12 LB/FT (1.8g/cm)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	11/26/19	MES	DWR	DWR	RELEASED TO PRODUCTION	V09002DZ

TITLE LOW SMOKE ZERO HALOGEN FIBERRUNNER 2X2 HINGED COVER (HC2L**2, HC2L**6) CUSTOMER DRAWING			
ITEM REVISION NAME 00501EAB/00			
DATASET FILE NAME 00501EAB_DC/00A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .03 [.8] .XXX ± .XX ± .03 [.8] ANGLES ±			MATERIAL: PC
THIRD ANGLE PROJECTION			DRAWING NUMBER: 00501EAB-DC
DRAWN BY MES	DATE 11-26-19	CHK DWR	SCALE NONE
SHT 1 OF 1			SIZE A

D10100DA/15