



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



CID**-C, PHONE OR DATA ICON LOCATED HERE, IDENTIFIES INDIVIDUAL PORT. OPTIONAL, NOT SUPPLIED.

PANDUIT PART NO.	WEIGHT (APPOX.)
DP48688TGY	2.2 lb (997.9 g)
DP48688TGWH	2.2 lb (997.9 g)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
- MATERIAL:
 PANEL HOUSING: STEEL
 RJ45 MODULES: THERMOPLASTIC RESIN UL94V-0
 PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
 BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
 RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
- 48 PORT PATCH PANEL 8 POSITION 8 WIRE.
- THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
- DIMENSIONS IN BRACKETS ARE IN METRIC.
- USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
- RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.

PART NUMBER DP48688TGY ; DP48688TGWH								
TITLE DP6 PLUS 48 PORT PATCH PANEL								
CUSTOMER DRAWING								
ITEM REVISION NAME M02479JE/01	PANDUIT							
DATASET FILE NAME M02479JE_DC241/01A								
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .xxx ± .010 (.3) .xx ± .03 (.8) ANGLES ±								
THIRD ANGLE PROJECTION								
DRAWN BY LZ	DATE 3-4-06							
CHK CEF	SCALE .25-1							
MATERIAL: SEE NOTE 2								
DRAWING NUMBER: 02479-241								
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	SHT 1 OF 1	SIZE A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	9-27-18	BAME	KRKE	MMR	B. ADDED P/N DP48688TGWH; C. REMOVED M6 SCREWS	M09000HW
1	5-22-14	MDJR	REFR	EJH	A. UPDATED TITLE BLOCK.	02479-241
R	3-04-06	LZ	CEF	CEF	RELEASED TO PRODUCTION	02479-241

D10100DA/14