


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
IUTP6X1MBLR	1 M	1.82 lbs/10 PCS (825.8 g/10 PCS)
IUTP6X2MBLR	2 M	3.64 lbs/10 PCS (1651.6 g/10 PCS)
IUTP6X3MBLR	3 M	5.46 lbs/10 PCS (2477.5 g/10 PCS)
IUTP6X5MBLR	5 M	9.10 lbs/10 PCS (4129.1 g/10 PCS)
IUTP6X10MBLR	10 M	18.20 lbs/10 PCS (8.258 kg/10 PCS)

NOTES:

- \*\*1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. CABLE MEETS CATEGORY 6A REQUIREMENTS.
5. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OR RoHS, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

T568B WIRING

PLUG POSITION	CABLE WIRE
1	WHITE ORANGE
2	ORANGE
3	WHITE GREEN
4	BLUE
5	WHITE BLUE
6	GREEN
7	WHITE BROWN
8	BROWN

PART NUMBER		IUTP6X**MBLR						
TITLE		CATEGORY 6A INDUSTRIALNET, UNSHIELDED PATCH CORD WITH ONE PLUG CAP						
		CUSTOMER DRAWING						
ITEM REVISION NAME		00251NAF/00		<b>PANDUIT</b>				
DATASET FILE NAME		00251NAF_DC02/00A						
		UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:				
		.x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ]		FMEA & CONTROL PLAN NUMBER:				
		.xx ± .01 [ .25 ]      ANGLES ± 5 °		INSPECTION INSTRUCTIONS NUMBER:				
		 THIRD ANGLE PROJECTION						
DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER:				
BJN	7-22-16	SCAL	NONE	00251NAF-02				
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	SHEET:	SIZE
							1 OF 1	A

R	7-22-16	BJN	SCAL	MBVE	RELEASED TO PRODUCTION	00251NAF-02		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	SHEET:	SIZE
							1 OF 1	A

2

1

2

1

D10100DA/14