

## THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		
Wire Size	600 kcmil		
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		
Wire Strip Length	1-13/16 in.		
Stud Size	1/2 in.		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90° C		
C.S.A Certified Wire Connector	Yes		
Panduit Color Code on Barrel	GREEN		
Panduit Die Index No. on Barrel	P94		
Alternate Industry Die Index No. () on Barrel	(22)		









						PANDUI	CORP. TINL	EY PARK, ILLINOIS
							LCAN600-12-6	
01	1/11	JHNU	JHNU	REVISED OVERALL LENGTH: WAS 4.20 REVISED TONGUE THICKNESS: WAS .27		Copper Lug - One-Hole, Narrow Tongue, Standard Barrel		
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A	DRAWING NO / CAD FILE	LCAN600-12-CUST