


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	"A" WIDTH	"B" WIDTH	"X" HEIGHT	"Y" HEIGHT	LABELS PER ROLL	MATERIAL	ADHESIVE
C225X450WJI	2.25 [ 57.2 ]	2.45 [ 62.2 ]	4.50 [ 114.3 ]	4.625 [ 117.5 ]	75	GMV19-R	STANDARD
C225X450WPI	2.25 [ 57.2 ]	2.45 [ 62.2 ]	4.50 [ 114.3 ]	4.625 [ 117.5 ]	75	GMV19-S	SUPERTACK
C350X500WJI	3.50 [ 88.9 ]	3.70 [ 94.0 ]	5.00 [ 127.0 ]	5.125 [ 130.2 ]	50	GMV19-R	STANDARD
C350X500WPI	3.50 [ 88.9 ]	3.70 [ 94.0 ]	5.00 [ 127.0 ]	5.125 [ 130.2 ]	50	GMV19-S	SUPERTACK
C400X200WJI	4.00 [ 101.6 ]	4.20 [ 106.7 ]	2.00 [ 50.8 ]	2.125 [ 54.0 ]	150	GMV19-R	STANDARD
C400X200WPI	4.00 [ 101.6 ]	4.20 [ 106.7 ]	2.00 [ 50.8 ]	2.125 [ 54.0 ]	150	GMV19-S	SUPERTACK
C400X400WJI	4.00 [ 101.6 ]	4.20 [ 106.7 ]	4.00 [ 101.6 ]	4.125 [ 104.8 ]	75	GMV19-R	STANDARD
C400X400WPI	4.00 [ 101.6 ]	4.20 [ 106.7 ]	4.00 [ 101.6 ]	4.125 [ 104.8 ]	75	GMV19-S	SUPERTACK
C400X600WJI	4.00 [ 101.6 ]	4.20 [ 106.7 ]	6.00 [ 152.4 ]	6.125 [ 155.6 ]	50	GMV19-R	STANDARD
C400X600WPI	4.00 [ 101.6 ]	4.20 [ 106.7 ]	6.00 [ 152.4 ]	6.125 [ 155.6 ]	50	GMV19-S	SUPERTACK



- NOTES:
1. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
  2. DIMENSIONS IN [ ] ARE METRIC.
  3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
  4. LABEL COLOR IS WHITE.
  5. FOR USE WITH PTM-C3500 PRINTER.

PART NUMBER		SEE TABLE		
TITLE				
VINYL COMPONENT LABEL ROLL FOR INK JET PRINTERS				
CUSTOMER DRAWING				
ITEM REVISION NAME		00211EBP/00		
DATASET FILE NAME		00211EBP_DC/00A		
		THIRD ANGLE PROJECTION		
MATERIAL		VINYL		
DRAWING NUMBER				00211EBP_DC
REV	DATE	BY	CHK	SCALE
00A	9/11/2020	ACC	DBLA	N/A
DESCRIPTION		ECN	SHEET 1 OF 1	
INITIAL RELEASE		088654	A	

A-SIZE CUSTOMER