THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.									
Μ	Material			High Conductivity Seamless Copper Tube					
Pl	Plating			Electro-Tin	.37 R Ref				
W	Wire Size			14 - 10 AWG STR, 12 - 10 AWG SOL					
W	Wire Type			Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric					
W	Wire Strip Length		1	7/16 in.	.42±.04				
St	Stud Size			1/4 in.					
	. Listed V onnecto			Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	2	25±.0427±.02 DIA			
	UL Temperature Rating			90°C			1.16±.06►		
	C.S.A Certified Wire Connector			Yes	Beveled wire				
	Panduit Color Code on Barrel		ode	N/A	\\/ir	e inspecti	entry		
	Panduit Die Index No. on Barrel		x No.	N/A		епъресп			
Di	Alternate Industry Die Index No. () on Barrel			N/A	.13±.01 .22±.01				
CERTIFIED US±.01									
								Υ	
								CORP. TINLEY PARK, ILLINOIS	
02	11/04	1/04 JHNU JHNU REVISED WIRE SIZE				12305	Copper Luç	LCA10-14-L g - One-Hole, Standard Barrel	
REV	DATE	DATE BY CHK DESCRIPTION				ECN	scale N/A	DRAWING NO / CAD FILE LCA10-14-CUST	