


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



**SPECIFICATION:**


- STANDARD  
 UNIT TYPE: BASIC  
 ORIENTATION: VERTICAL, 0U MID  
 OUTLET QTY & TYPE: (20)C13, (4)C19  
 INPUT VOLTAGE: 100-240VAC  
 INPUT FREQUENCY: 50/60HZ  
 INPUT CURRENT: 16A  
 BREAKER QTY & TYPE: NONE  
 INPUT PHASE: SINGLE-PHASE  
 RATED POWER: 3.7 kVA  
 INPUT PLUG: IEC 60309 2P+E 6H 16A  
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE  
 REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL:  
 NONE
- ACCESSORIES:  
 DOCUMENTATION KIT  
 PRODUCT SAFETY WARNING SHEET

**NOTES:**


- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION:**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E24B10M-XXYZ



**PLUG / RECEPTACLE BLOCK**





00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24B10M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE <b>INTELLIGENT SERIES PDU E24B10M</b> CONTROL DRAWING		
ITEM REVISION NAME:		<b>PANDUIT</b>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN] Tolerance (mm) 0 < L ≤ 50 ± 0.5 50 < L ≤ 250 ± 1.0 250 < L ≤ 500 ± 1.5 500 < L ≤ 1000 ± 2.5 1000 < L ≤ 2000 ± 4.0		MATERIAL / COLOR: <b>N/A</b>
THIRD ANGLE PROJECTION		DRAWING NUMBER: <b>E24B10M_DC</b>
DRAWN BY LL	DATE 08/29/2023	CHK MIM
SCALE NONE	SHT 1 OF 2	
		SCALE <b>B</b>

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E24B10M	BASIC PDU, 16A, (20)C13 (4)C19, IEC 60309 2P+E 6h IP44-3M, TOP-FED, BLACK	BLACK(RAL 9005)	3M(+254MM/-127MM)[10'(+10"/-5"']	4.2kg

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24B10M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE <b>INTELLIGENT SERIES PDU E24B10M</b> CONTROL DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance (mm) 0 < L ≤ 50 ±0.5 50 < L ≤ 250 ±1.0 250 < L ≤ 500 ±1.5 500 < L ≤ 1000 ±2.5 1000 < L ≤ 2000 ±4.0		N/A
 THIRD ANGLE PROJECTION		DRAWING NUMBER:
DRAWN BY: LL    DATE: 08/29/2023    CHK: MIM    SCALE: NONE		<b>E24B10M_DC</b>
		SHT 2 OF 2
		SCALE: <b>B</b>