HIS COPY IS F	PROVID	DED ON	A RESTRICTED BASIS AND IS NOT TO BE USI		DETRIMENTA			ERESTS OF PANDUIT CORP			
Material			High Conductivity Seamless Copper Tube								
Plating			Electro-Tin								
Wire Size			2 AWG	.38 R REF							
Wire Type			Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		.60±.04	₿	STR CU			PANDUIT	
Wire Strip Length			1-1/4 in.							BROWN DIE P33 (10)	
Stud Size			1/4 in.								
UL Listed Wire Connector			Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.25±.0427±.02 DIA Color coded barrel markings							
UL Temperature Rating			90° C								
C.S.A Certified Wire Connector			Yes	.42±.01 .31±.01							
Panduit Color Code on Barrel			BROWN		1.16±.04						
Panduit Die Index No. on Barrel		ex No.	P33								
Alternate Industry Die Index No. () on Barrel			(10)	Wire ins	oection wind	low—			1	I.37 REF	
CERTIFIED LISTED										•	
			Wire Connector	.10±.01				1.68 REF			
								ZANDU	CORP.	TINLEY PARK, ILLINOIS	
									LCB2-14WH-0		
) 4/17 JHNU JHNU			DRAWING RELEASED		RGB		SCALE	DRAWING NO / CAD F	ILE		
EV DATE	BY	СНК	DESCRIPTION		ECN	-R	205	N/A		LCB2-14WH-CUST	