





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



SPECIFICATION:


1. STANDARD:
- UNIT TYPE: SEE SHEET 2
 - ORIENTATION: VERTICAL, 0U, FULL
 - OUTLET QTY&TYPE: (20) C13, (4) C19
 - INPUT VOLTAGE: 200-240VAC
 - INPUT CURRENT: 32A
 - BREAKER QTY&TYPE: (2) 16AMP, SINGLE-POLE
 - INPUT PHASE: SINGLE-PHASE
 - RATED POWER: 7.4kVA
 - INPUT PLUG: IEC 60309 2P+E 6H 32A
 - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
 - REGULATORY STANDARD: RoHS COMPLIANT
2. ADDITIONAL: NONE
3. ACCESSORIES: (1) QUICK-START GUIDE

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION
- PARTS USING UPGRADEABLE IPDU BLANKING PANEL CAN BE UPGRADED TO INTELLIGENT MODELS USING PANDUIT CONTROLLER PART NUMBER MA002

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24E01M-XX Y Z



BOTTOM VIEW

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____
DATE _____
PRINT _____

PLUG/RECEPTACLE BLOCK

PLUG
IEC 60309, 2P 3W, 6H
IP44 (SPASHPROOF)
32A, 200-250V MAX RATED INPUT

RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT

RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	05/13/2022	FYZ	MIM	MJD	1. ADDED UPGRADEABLE PDU OPTION 2. REMOVED OBSOLETE SKU'S	P24E01M
03A	06/15/2018	LWB	MIM	JAWI	UPDATED THE OUTLET DESIGN	P24E01M
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION "DE-CODER"	P24E01M
01A	07/13/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24E01M

TITLE INTELLIGENT SERIES PDU P24E01M-XXYZ CUSTOMER DRAWING	
ITEM REVISION NAME:	
DATASHEET FILE NAME:	
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]	
Tolerance(mm)	
0-1<50	±0.5
50-1<250	±1.0
250-1<500	±1.5
500-1<1000	±2.5
1000-1<2000	±4.0
DRAWN BY DATE GEORGE 06/27/2017	
CHK SEAN	SCALE NONE
DRAWING NUMBER: P24E01M_DC	
SHT 1 OF 2	
SCALE B	

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

MAIN PDU CONFIGURATIONS				
FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24E01M	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.5kg
P24E01M-BL1A	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P24E01M-RD1A	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P24E01M-RD1C	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.5kg
P24E01M-YL1A	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P24E01M-YL1C	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.5kg
P24E01M-BU1A	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P24E01M-BU1C	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.5kg
P24E01M-BL2A	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P24E01M-BL2C	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.5kg
P24E01M-RD2A	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P24E01M-RD2C	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.5kg
P24E01M-YL2A	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P24E01M-YL2C	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.5kg
P24E01M-BU2A	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P24E01M-BU2C	VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.5kg
UPGRADEABLE PDU CONFIGURATIONS				
FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24E01U	UPGRADEABLE,VERTICAL,(20) C13,(4) C19,MONITORED SWITCHED, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.2kg

B

B



A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	05/13/2022	FYZ	MIM	MJD	1.ADDED UPGRADEABLE PDU OPTION 2.REMOVED OBSOLETE SKU'S	P24E01M
03A	06/15/2018	LWB	MIM	JAWI	UPDATED THE OUTLET DESIGN	P24E01M
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION "DE-CODER"	P24E01M
01A	07/13/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24E01M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P24E01M-XYZ CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
Tolerance(mm) 0.1<50 ±0.5 50<250 ±1.0 250<500 ±1.5 500<1000 ±2.5 1000<2000 ±4.0		DRAWING NUMBER: P24E01M_DC
DRAWN BY GEORGE	DATE 06/27/2017	SCALE NONE
CHK SEAN	SHT 2 OF 2	
		SCALE B

2



1