



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	WEIGHT
DPA245E88TGY	1.26 lb (571.53 g)
DPA245E88TWH	1.26 lb (571.53 g)

- NOTES:
- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
 - MATERIAL:
 PANEL HOUSING: STEEL
 RJ45 MODULES: THERMOPLASTIC RESIN UL94V-0
 PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
 BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
 RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
 - 24 PORT ANGLED PATCH PANEL 8 POSITION 8 WIRE.
 - THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
 - FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
 - DIMENSIONS IN BRACKETS ARE IN METRIC.
 - USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
 - RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.



PART NUMBER
DPA245E88TGY ; DPA245E88TGWH


TITLE
DP5E 24 PORT ANGLED PATCH PANEL
 CUSTOMER DRAWING

ITEM REVISION NAME
M02479JH/02
 DATASET FILE NAME
M02479JH_DC244/02A



UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE: IN [mm]
 .x ± .xxx ± .010 [.3]
 .xx ± .03 [.8] ANGLES ±

MATERIAL:
SEE NOTE 2



DRAWING NUMBER:
02479-244

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	5-4-18	BAME	KRKE	MMR	B. ADDED P/N DPA245E88TGWH; C. REMOVED M6 SCREWS	M09000HW
2	5-30-14	MDJR	REFR	MMR	A. UPDATED TITLE BLOCK. PREVIOUS REVISIONS REMOVED FOR CLARITY.	02479-244

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
MDJR	5-30-14	REFR			A

D10100DA/14