
Mini-Com[®] All Metal Shielded **Modular Patch Panels**



SPECIFICATIONS

All metal modular patch panels shall be made of stainless steel and mount to standard racks and cabinets. All metal patch panels shall accept all Mini-Com Shielded Jack Modules for shielded installations. Patch panel write-on areas and optional adhesive labels shall identify each port and panel. Angled all metal modular patch panels shall be available in standard density 24- and 48-ports. Flat all metal modular patch panels shall be available in standard density 24- and 48-port. Flat design in 24 and 48-ports shall also be available with built-in strain relief bar with unique features to support individual cables.





TECHNICAL INFORMATION

Mounting option:	Mounts to standard EIA 19" rack, or 23" rack when used with extender brackets (PEB1 or PEB2) or cabinet
Packaging:	Includes mounting screws (#12-24) and CPT tool for easy removal of Mini-Com Modules
Material:	Stainless steel

KEY FEATURES AND BENEFITS

Modular:	Mini-Com Shielded Jack Modules snap in and out of all Mini-Com All Metal Shielded Modular Patch Panels for easy moves, adds, and changes	
Identification:	Dedicated areas allow for port and panel identification with optional adhesive labels	
Built-in strain relief bar:	Secures individual cables and provides proper cable support (CP24WSBLY and CP48WSBLY)	
Patented angled design:	Allows cable to flow to each side of the rack and minimizes the need for horizontal cable managers; increase risk and closet density	
Strain relief bars (optional)	Different styles available to help manage and route rear cables	
Angled filler panels (optional)	Reserves space for future use and promotes proper airflow and cooling	

APPLICATIONS

Mini-Com All Metal Shielded Modular Patch Panels and Mini-Com Shielded Jack Modules are ideal for use in shielded cabling installations. Angled patch panels minimize the use of horizontal cable managers by allowing the cables to flow directly into vertical cable managers, thus increasing rack density. Selected flat patch panels include a built-in strain relief bar that offers integrated cable tie slots and a 1.46" surface to manage and support individual cables. Mini-Com Shielded Jack Modules bond to the panel when snapped into a Mini-Com All Metal Shielded Modular Patch Panel. When installing the patch panel on the rack, the use of patentpending thread-forming bonding screws bond the shielded panel to the rack. The combination of all-metal patch panels, shielded jack modules and accessories provide a properly grounded system.


Angled Shielded Patc	h Panels				
24-port, 1 RU:	CPA24*				
4 8-port, 2 RU:	CPA48**				
Flat Shielded Patch P	anels				
24-port, 1 RU:	CP24*				
48-port, 2 RU:	CP48*				
Flat Shielded Patch P Strain Relief Bar	anels with				
24-port, 1 RU:	CP24WSBLY				
48-port, 2 RU:	CP48WSBLY				
Mini-Com Shielded Jack Modules					
Category 6A:	CJS6X88TGY				
Category 6:	CJS688TGY				
Category 5e:	CJS5E88TGY				
Patch Panel Accessories					
1 RU angled:	CPAF1*				
2 RU angled:	CPAF2*				
1 RU flat:	DPFP1 [^]				
2 RU flat:	DPFP2 [^]				
Transitional covers:	CPATC*				
Strain Relief Bars and	d Accessories				
Strain relief bar with clips:	SRBWCY				
Strain relief bar (straight):	SRBS19BL-XY				
Strain relief bar (U-shaped):	SRB19BLY				
High-density strain relief bar manager:	SRBM19BLY				
Strain relief bar brackets:	SRBBRKT				
Thread Forming Bonding Screws					
#12-24 English:	RGTBSG-C				
M6 Metric:	RGTBSM6G-C				


*Colors: BLY (Black) or WH (White) ^Colors other than Black: WH (White)


LABEL CHART

Part numbers with labeling options:	Label Type	Laser/Ink	Laser/InkJet
CP24BLY	Adhesive	C252X030YPT	C252X030FJJ
CPA24BLY			
CP48BLY			
CPA48BLY			
CP24WH			
CPA24WH			
CP48WH			
CPA24WH			
CP24WSBLY			
CP48WSBLY			

ENGINEERING DRAWING







CP48WSBLY

Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

© 2024 Panduit Corp. ALL RIGHTS RESERVED. COSP494-WW-ENG 4/2024