



Tool Chart for Compression Connectors Type S-R with Copper Cable

			CT-1700 ^①	CT-720	CT-810 ^④	CT-1250 ^④	CT-2600/L CT-2600/LINT CT-2600/LUK CT-2600/LAUS CT-2600/TO	A See Tool List Below	B See Tool List Below	C See Uni-Die™ Dieless Tools Below	CT-3980 CT-3980/INT CT-3980/UK CT-3980/AUS CT-3980/TO Uni-Die™ Dieless Tool
Panduit Part Number	Std. Wire Size	Wire Strip Length	Panduit Die Part Number Die Index Number (Number of Crimps)								
S8	#8 AWG	7/16"	P21 (2)	CD-720-1 P21 (1)	8 AWG Red (1)	---	KC4-8 Red (1)	CD-2001-8 P21 (1)	CD-920-8 P21 (1)	---	STD (1)
S6	#6 AWG	1/2"	P24 (2)	CD-720-1 P24 (1)	6 AWG Blue (1)	---	KC4-6 Blue (1)	CD-2001-6 P24 (1)	CD-920-6 P24 (1)	---	STD (1) #4 AWG STR, #2 AWG SOL
S4	#4 AWG	1/2"	P29 (2)	CD-720-1 P29 (1)	4 AWG Gray (1)	---	KC4-4 Gray (1)	CD-2001-4 P29 (1)	CD-920-4 P28 (1)	STD (1)	STD (1)
S2	#2 AWG	5/8"	P37 (3)	CD-720-2 P37 (1)	2 AWG Brown (1)	---	KC4-2 Brown (1)	CD-2001-1 P37 (1)	CD-920-1 P37 (1)	STD (1)	STD (1)
	#1 AWG	5/8"		CD-720-2 P37 (1)	1 AWG Green (1)	1 AWG Green (1)	KC4-2 Brown (1)	CD-2001-1 P37 (1)	CD-920-1 P37 (1)	STD (1)	STD (1)
S1/0	1/0 AWG	5/8"	---	CD-720-2 P42 (1)	1/0 AWG Pink (1)	1/0 AWG Pink (1)	KC4-1/0 Pink (1)	CD-2001-1/0 P42 (1)	CD-920-1/0 P42 (1)	STD (1)	STD (1)
S2/0	2/0 AWG	11/16"	---	CD-720-2 P45 (2)	---	2/0 AWG Black (2)	KC4-2/0 Black (2)	CD-2001-2/0 P45 (2)	CD-920-2/0 P45 (1)	STD (1)	STD (1)
S3/0	3/0 AWG	7/8"	---	CD-720-2 P50 (2)	---	---	KC4-3/0 Orange (2)	CD-2001-3/0 P50 (2)	CD-920-3/0 P50 (1)	STD (1)	STD (1)
S4/0	4/0 AWG	15/16"	---	CD-720-3 P54 (2)	---	4/0 AWG Purple (2)	KC4-4/0 Purple (2)	CD-2001-4/0 P54 (2)	CD-920-4/0 P54 (1)	STD (1)	STD (1)
S250	250 kcmil	1-1/16"	---	CD-720-3 P62 (2)	---	---	KC4-250 Yellow (2)	CD-2001-250 P62 (2)	CD-920-250 P62 (1)	STD (1)	STD (1)

- ①The CT-1700 crimp die pockets are integrated into the tool frame.
 ③CD-920 dies can be used with CT-940CH series and CT-2940 series tools with die adapter.
 ④ Rotate gauge selector to the indicated gauge setting

A CT-2001, CT-2001/L, CT-2001/LE, CT-2002, CT-2002/L, CT-3001, CT-3001/E, CT-3001/ST, CT-3001/STINT, CT-3001/STUK, CT-3001/STAUS, CT-3001/TO, CT-3001/CCP, CT-3001/CCPINT, CT-3001/CCPUK, CT-3001/CCPAUS, CT-3001/CCPTO

B CT-920, CT-920/CV, CT-920CH, CT-920CH/CV, CT-920CH/CCP, CT-930, CT-930CH, CT-930LPCH, CT-940CH^③, CT-2920, CT-2920/CCP, CT-2920/CCPINT, CT-2920/CCPUK, CT-2920/CCPAUS, CT-2920/CCPTO, CT-2930, CT-2930/L, CT-2930/LE, CT-2931, CT-2931/ST, CT-2931/STINT, CT-2931/STUK, CT-2931/STAUS, CT-2931/TO, CT-2931/STCV, CT-2931/STCVINT, CT-2931/STCVUK, CT-2931/STCVAUS, CT-2931/CVTO, CT-2940^③, CT-2940/L^③, CT-2940/LE^③, CT-2940/ST^③, CT-2940/STINT^③, CT-2940/STUK^③, CT-2940/STAUS^③, CT-2940/TO^③

C CT-980, CT-980CH, CT-980LPCH, CT-2950, CT-2980, CT-2980/L, CT-2980/LE, CT-2980/ST, CT-2980/STINT, CT-2980/STUK, CT-2980/STAUS, CT-2980/TO, CT-2981



For Instructions in Local Languages
and Technical Support:

PANDUIT

www.panduit.com/resources/install_maintain.asp

www.panduit.com

E-mail:
cs@panduit.com

Fax:
708-444-6993