

NOTES:

- CONNECTORS MEET REQUIREMENTS OF TIA-568-C.3.
- ALL MATERIALS AND COMPONENTS MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- FOR PERFORMANCE REQUIRMENTS OR LENGTHS OTHER THAN THOSE SPECIFIED, CONTACT PANDUIT.

FIBER TYPE
 9 - SINGLEMODE OS2 (YELLOW JACKET)
 X - 50/125 OM3 (AQUA JACKET)
 Z - 50/125 OM4

FIBER COUNT
 T - 12 FIBERS

JACKET FLAME RATING
 R - OFNR

CONNECTOR
 1 - LC
 3 - SC


CONNECTOR VARIANT
 7 - 18" BREAKOUT

PERFORMANCE
 S - STANDARD PERFORMANCE

UNIT OF MEASURE
 M - METERS

LENGTH
 001 - 1 METER
 002 - 2 METERS
 003 - 3 METERS

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
F		T	S	R		7	N	N	S	N	M			



							TITLE PRETERMINATED 12 STRAND LC/SC FIBER OPTIC PIGTAIL CUSTOMER DRAWING					
							ITEM REVISION NAME M00997BJ/00					
							DATASET FILE NAME M00997BJ_DC/00B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x : .03 [.762] .xxx : .005 [.127] .xx : .01 [.25] ANGLES : 1 °					
							THIRD ANGLE PROJECTION					
00B	05-12-17	SAT	WMA	RWB	RELEASED TO PRODUCTION	M00997BJ-DC	DRAWING NUMBER: M00997BJ-DC					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 09-23-14	CHK WMA	SCALE NONE	SHT 1 OF 1	SIZE B