EV DATE	BY	СНК	DESCRIPTION	ECN	-R	SUP	SCALE N/A DRAWING NO / CAD FILE LCB2/0-38W-CUST	
0 6/17		JHNU	DRAWING RELEASED	021775	RGB	RGB		
							CORP. TINLEY PARK, ILLINO	
	CE	RTIFIED	 LISTED Wire Connector 	.13	+		.45±.01 .58±.01	
Alternate Industry Die Index No. () on Barrel			(13)	Wire inspe	ection	on window		
Panduit Die Index No. on Barrel		ex No.	P45	Beveled wir				
Panduit Color Code on Barrel		ode	BLACK					
C.S.A Certified Wire Connector			Yes	2.67±.06				
UL Temperature Rating			90° C					
UL Listed Wire Connector			Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.39±.04				
Stud Size			3/8 in.		\downarrow	2/02		
Wire Strip Length		n	1-9/16 in.	.85±.04	PANDUIT 2/0 STR CU LCB2/0-38W PANDUIT			
Wire Type			Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric					
Wire Size			2/0 AWG		Г		— .45 R REF Color coded	
Plating			Electro-Tin					
Material			High Conductivity Seamless Copper Tube					