HIS COPY IS PROVIDED ON	A RESTRICTED BASIS AND IS NOT TO BE	JSED IN ANY WAY DETRIMENT			RESTS OF PANDUIT CORP.		
Material	High Conductivity Seamless Copper Tube						
Plating	Electro-Tin				.51	R Ref	
Wire Size	4/0 AWG	-					
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		1			(15)	1
Wire Strip Length	1-5/8 in.	1	ا 06±.04	INDN (A/0 STR CU 4/0 STR CU BANDUIT	URPLE DIE P54 (15)	
Stud Size	3/8 in.			PA		PURFL	
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.3'	 9±.04 -		.41±.02 DIA		
UL Temperature Rating	90° C			-	2.85±.06		
C.S.A Certified Wire Connector	Yes						
Panduit Color Code on Barrel	PURPLE						
Panduit Die Index No. on Barrel	P54				1.56	5±.04 ——	Beveled wire entry
Alternate Industry (15) Die Index No. () on Barrel		Wire inspection window					
CERTIFIED	 LISTED Wire Connector 	.14±.0					.57±.01 .71±.01
0 6/07 JHNU JHNU	DRAWING RELEASED	021775	RGB	RGB		34/0-380	TINLEY PARK, ILLINOIS /-X 9 Barrel with Window