



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- DIMENSIONS IN [ ] ARE METRIC.
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- PART INCLUDES:
  - 1- TEE BASE
  - 2- SUPPORT BRACKET
  - 2- BEND RADIUS PROTECTOR
  - 8- C-CLIPS
  - 11- KEPS NUTS
  - 4- CABLE TIE
  - 8- PLASTIC RIVET
  - 3- CARRIAGE BOLT
  - 3- PLATE CLAMP

PART NUMBER	NOMINAL SIDEWALL HEIGHT	FINISH	WEIGHT
PWBPF2X6BL	2" (50mm)	BLACK POWDER	4.5 LBS/EACH (2041.2)g/EACH
PWBPF2X6WH		WHITE POWDER	
PWBPF2X6EZ		CLEAR ZINC	
PWBPF4X6BL	4" (100mm)	BLACK POWDER	4.7 LBS/EACH (2131.9)g/EACH
PWBPF4X6WH		WHITE POWDER	
PWBPF4X6EZ		CLEAR ZINC	
PWBPF6X6BL	6" (150mm)	BLACK POWDER	4.9 LBS/EACH (2222.6)g/EACH
PWBPF6X6WH		WHITE POWDER	
PWBPF6X6EZ		CLEAR ZINC	

TITLE <b>WIRE BASKET FORMED TEE FITTING 6" (150mm) W</b>														
CUSTOMER DRAWING														
ITEM REVISION NAME <b>00510JAM/00</b>														
DATASET FILE NAME <b>00510JAM_DC/00C</b>														
MATERIAL <b>C.R.S.</b>														
DRAWN BY <b>JSP</b>					DATE <b>6/1/21</b>		CHK <b>WJM</b>		SCALE <b>NONE</b>					
DRAWING NUMBER <b>00510JAM-DC</b>					SHEET 1 OF 1									
REV					DESCRIPTION					ECN				

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00C	12-15-23	SAT	DWR	EB	D. ADDED METRIC HEIGHTS. B. UPDATED TITLE. C. REMOVED P/N FROM TITLEBLOCK.	00510JAM-DC
00B	4/18/22	JSP	DWR	ML	A. UPDATED COMPONENT LIST.	00510JAM-DC
00A	6/1/21	JSP	WJM	ML	INITIAL RELEASE	00510JAM-DC

A-SIZE CUSTOMER