
	DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.
--	---


Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		
Wire Size	6 AWG		
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		
Wire Strip Length	7/8 in.		
Stud Size	1/4 in.		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90° C		
C.S.A Certified Wire Connector	Yes		
Panduit Color Code on Barrel	BLUE		
Panduit Die Index No. on Barrel	P24		
Alternate Industry Die Index No. () on Barrel	(7)		






LISTED Wire Connector







						CORP. TINLEY PARK, ILLINOIS
						LCA6-14F-L
01	5/06	DRL	DRL	ADDED UL, CSA AND PART NO. TO STAMP	PC00450	Copper Lug - One-Hole, Standard Barrel, 90° Angle Tongue
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCA6-14F-CUST