




- NOTES:
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
  - DIMENSIONS IN [ ] ARE mm.
  - PART INCLUDES
    - A. 1 - 24 PORT SHIELDED KEYSTONE 1RU ANGLED PATCH PANEL, LONG STRAIN RELIEF BAR.
    - B. 1 - 18AWG GROUND WIRE ASSEMBLY, OVERALL LENGTH 40cm IN LENGTH.
    - C. 4 - MOUNTING SCREWS
    - D. 4 - MOUNTING WASHERS
    - E. 4 - MOUNTING NUTS
    - F. 25 - CABLE TIES
  - WEIGHT: 2LBS/PCS IN PACKAGING
  - ALL MATERIALS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00B	9-11-20	BJN	VJV	SKH	A. CORRECTED P/N TO READ KP24APWSBL	00326EAL-DC
00A	4-14-20	BJN	VJV	AMN/SKH	RELEASED TO PRODUCTION	00326EAL-DC

PART NUMBER	KP24APWSBL	PACKAGING SPEC	N/A
PRODUCT SPEC	N/A	WORK INSTRUCTION	N/A
INSPECTION INSTRUCTION NUMBER	N/A	FMEA & CONTROL PLAN NUMBER	N/A
TITLE			
24 PORT SHIELDED KEYSTONE™ 1RU ANGLED-PORT PATCH PANEL, LONG STRAIN RELIEF BAR			
CUSTOMER DRAWING			
ITEM REVISION NAME	00326EAL/00		
DATASET FILE NAME	00326EAL_DC/00B		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
.x ± .1 [ 2.54 ]	.xxx ± .005 [ .127 ]	DRAWING NUMBER: 00326EAL - DC	
.xx ± .01 [ .25 ]	ANGLES ± 1°		
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
BJN	4-8-20	VJV	NONE
SHT 1 OF 1			SIZE B

NXGLOBAL\_BSIZE