



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
P24D03M-XYZ	SEE SHEET 2




LEFT VIEW




REAR VIEW



RIGHT VIEW



FRONT VIEW



BOTTOM VIEW

**SPECIFICATION:**

1. STANDARD:
- UNIT TYPE: MONITORED INPUT
  - ORIENTATION: VERTICAL, MID
  - OUTLET QTY&TYPE: (20) C13, (4) C19
  - INPUT VOLTAGE: 200-240VAC
  - INPUT CURRENT: 32A
  - BREAKER QTY&TYPE: (2) 16AMP, SINGLE-POLE
  - INPUT PHASE: SINGLE-PHASE
  - RATED POWER: 7.4kVA
  - INPUT PLUG: IEC 60309 2P+E 6H 32A
  - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
  - REGULATORY STANDARD: RoHS COMPLIANT
2. ADDITIONAL: NONE
3. ACCESSORIES: (1) QUICK-START GUIDE

**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [ INCHES ] .
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES .
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART .
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL .
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION**


FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24D03M-XX Y Z

XX: FINISHED GOOD COLOR BL=BLACK YL=YELLOW RD=RED BU=BLUE WH=WHITE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
--	---	---


**PLUG/RECEPTACLE BLOCK**



PLUG  
IEC 60309, 2P 3W, 6H  
IP44 (SPASHPROOF)  
32A, 200-250V MAX RATED INPUT



RECEPTACLES  
IEC 60320/C19  
16A, 250V MAX RATED OUTPUT



RECEPTACLES  
IEC 60320/C13  
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER'	P24D03M
01A	07/13/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24D03M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P24D03M-XYZ CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER: P24D03M_DC
DRAWN BY GEORGE	DATE 06/27/2017	SCALE NONE
CHK SEAN	SHT 1 OF 2	
		SCALE B

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24D03M	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-BL1A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-BL1B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-RD1A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-RD1B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-RD1C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-WH1A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-WH1B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-WH1C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-YL1A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-YL1B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-YL1C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-BU1A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-BU1B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-BU1C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-GN1A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-GN1B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-GN1C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, TOP-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-BL2A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-BL2B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-BL2C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-RD2A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-RD2B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-RD2C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-WH2A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-WH2B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-WH2C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-YL2A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-YL2B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-YL2C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-BU2A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-BU2B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-BU2C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg
P24D03M-GN2A	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+89mm/-45mm) 3.3'[+3.5"/-1.75"]	5.8kg
P24D03M-GN2B	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178mm/-89mm) 6.5'[+7"/-3.5"]	6.3kg
P24D03M-GN2C	VERTICAL,(20) C13,(4)C19,MONITORED INPUT, 200-240V/32A / 1 PHASE, BOTTOM-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254mm/-127mm) 10'[+10"/-5"]	6.8kg

B

B

A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P24D03M-XYZ CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
 THIRD ANGLE PROJECTION		N/A
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		DRAWING NUMBER: P24D03M_DC
DRAWN BY	DATE	CHK
GEORGE	06/27/2017	SEAN
SCALE	NONE	
SHT 2 OF 2		SCALE B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO I NCLUDE CONFIGURABLE OPTION 'DE-CODER'	P24D03M
01A	07/13/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24D03M

2



1