

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P42D21M-XXYZ	SEE SHEET 2

SPECIFICATION:

1. STANDARD:

UNIT TYPE: MONITORED INPUT
 ORIENTATION: VERTICAL, 0U FULL
 OUTLET QTY & TYPE: (21)C13/C15,(21)C13/C15/C19
 INPUT VOLTAGE: 200-240/346-415VAC
 INPUT CURRENT: 60A (48A DERATED)(NA)/63A(EU)
 BREAKER QTY & TYPE: (12) 20AMP, SINGLE-POLE, 10KA
 INPUT PHASE: THREE-PHASE, WYE
 RATED POWER: DUAL-RATED: 34.6 kVA (NA)/43.5 kVA(EU)
 INPUT PLUG: IEC 60309, 3P+N+E, 6H, 60A/63A(IP44)
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
 REGULATORY STANDARD: RoHS COMPLIANT

2. ADDITIONAL:

NONE

3. ACCESSORIES:




(1) QUICK-START GUIDE

NOTES:

1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES] .
2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES .
3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART .
4. FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL .
5. DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P42D21M-XX Y Z



XX: FINISHED GOOD COLOR BL=BLACK YL=YELLOW RD=RED BU=BLUE WH=WHITE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
--	---	---

PLUG/RECEPTACLE BLOCK

PLUG
IEC 60309, 3P+N+E, 6H
IP44(SPLASHPROOF)
DUAL RATED 60A
(48A DERATED)/63A 346-415V MAX
RATED INPUT

RECEPTACLES
C13/C15 COMBO
10A, 250V MAX RATED OUTPUT

RECEPTACLES
C13/C15/C19 COMBO
16A, 250V MAX RATED OUTPUT

01A	11/25/2022	LRF	CSH	MJD	INITIAL RELEASE	P42D21M-XXYZ
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN
DATE
PRINT

TITLE: INTELLIGENT SERIES PDU
P42D21M-XXYZ
CONTROL DRAWING

ITEM REVISION NAME:
DATASHEET FILE NAME:

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCE ARE: mm [IN]

Tolerance(mm)	
0.4<50	±0.5
50<4200	±1.0
2500<4000	±1.5
500<1000	±2.5
1000<2000	±4.0

THIRD ANGLE PROJECTION

MATERIAL/COLOR: N/A

DRAWING NUMBER: P42D21M-XXYZ_DC

SCALE: SHT 1 OF 2

