
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube			
Plating	Electro-Tin			
Wire Size	4/0 AWG			
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric			
Wire Strip Length	1-5/8 in.			
Stud Size	1/2 in.			
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.			
UL Temperature Rating	90° C			
C.S.A Certified Wire Connector	Yes			
Panduit Color Code on Barrel	PURPLE			
Panduit Die Index No. on Barrel	P54			
Alternate Industry Die Index No. () on Barrel	(15)			






Wire Connector



PANDUI'

URPLE DIE P54 (1

LCB4/0-12WH-CUST



								CORP. TINLEY PARK, ILLINOIS
								LCB4/0-12WH-X Copper Lug - One-Hole, Long Barrel with Window, 45° Angle Tongue
00	4/17	JHNU	JHNU	DRAWING RELEASED	021775	RGB	RGB	

SUP SCALE DRAWING NO / CAD FILE REV DATE BY CHK **DESCRIPTION ECN** -R N/A