Material	High Conductivity Seamless Copper Tube			
Plating	Electro-Tin	.63 R Ref		
Wire Size	6 AWG	BLUE DIE P24 (7)		
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	.750±.04 English Significant Color coded		
Wire Strip Length	7/8 in.	barrel markings		
Stud Size	1/2 in.	.63±.0453±.02 DIA (2) PLS		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.			
UL Temperature Rating	90° C	Beveled wire entry—		
C.S.A Certified Wire Connector	N/A	22±.01		
Panduit Color Code on Barrel	BLUE	.81±.04		
Panduit Die Index No. on Barrel	P24	Wire inspection window 45°±5° .97 REF		
Alternate Industry Die Index No. ( ) on Barrel	(7)			
	c (UL) us	12±.01 — 3.79 REF		
Die Index No. ( ) on Barrel		3.79 REF		

						CORP. TINLEY PARK, ILLINOIS
00	6/17	ILIKILI	JHNU	DRAWING RELEASED	022679	LCD6-12H-L Copper Lug - Two-Hole, Standard Barrel, 45° Angle Tongue
REV	DATE	ВҮ	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCD6-12H-CUST