


2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. TERMINATES 22-26AWG SOLID OR STRANDED UTP CABLE
2. COMPATIBLE WITH CABLE JACKET  $\phi$  0.189" (4.8mm) - 0.272" (6.9mm)
3. PARTS INCLUDED  
 2 END CAPS: POLYCARBONATE  
 1 MAIN SPLICE MODULE: POLYCARBONATE  
 2 WIRE CAPS: POLYCARBONATE W/ PRINTED WIRE MAPPING  
 2 STRAIN RELIEF COLLARS: POLYCARBONATE
4. DIMENSIONS IN [ ] ARE IN METRIC.



PART NUMBER		FC-ISC		
TITLE				
<b>FIELDCORD™ INDOOR SPLICE CONNECTOR</b>				
CUSTOMER DRAWING				
ITEM REVISION NAME		01128EAC/00		
DATASET FILE NAME		01128EAC_DC/00A		
		THIRD ANGLE PROJECTION		
MATERIAL		SEE NOTES		
DRAWING NUMBER				01128EAC-DC
REV	DATE	BY	CHK	APR
00A	3-4-22	ROJC	REFR	JNU
INITIAL RELEASE				
DESCRIPTION		ECN		
DRAWN BY	DATE	CHK	SCALE	SIZE
ROJC	3-4-22	REFR	NONE	A
SHEET 1 OF 1				

A-SIZE CUSTOMER

2

1