



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOMINAL DUCT SIZE (W)	"A" LENGTH/TOLERANCE INCH [mm]	"B" LENGTH/TOLERANCE MM [inch]	"C" WIDTH INCH [mm]	"TC" THICKNESS INCH [mm]	"HC" HEIGHT INCH [mm]
.5	72.00 ±.18 [1828.8 ±4.5]	N/A	.69 [17.5]	.040 [1.0]	.230 [5.8]
.75		2000.00 ±4.5 [78.74 ±.18]	.94 [23.9]	.050 [1.3]	.240 [6.1]
1			1.25 [31.8]	.060 [1.5]	.350 [8.9]
1.5			1.75 [44.5]		
2		N/A	2.25 [57.2]	.065 [1.6]	.370 [9.4]
2.5		2000.00 ±4.5 [78.74 ±.18]	2.75 [69.9]		
3	3.25 [82.6]				
4			4.25 [108.0]		
6			6.25 [158.8]		

NOTES:

- SEE www.panduit.com FOR COLOR AND PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX.
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVLENT [mm] or [inch].



PART NO. SYSTEM COVER EXAMPLE
 TYPE C 2 LG 2
 WIDTH (inch) COLOR LENGTH (FT) or (M)

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:	DRAWING NUMBER:
							WIRING DUCT COVER TYPE "C" FOR DUCT TYPES D, F, FS, G AND FIBER DUCT	PANDUIT	
							CUSTOMER DRAWING		
							ITEM REVISION NAME D34078CB/05		
							DATASET FILE NAME D34078CB_DC/01A		
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCH [mm]		
1	02-01-17	JBN	MRJS	RGRO	A. ADDED COVER SIZES IN 2M LENGTH: C.75 & C6	D34078CB-DC	.X ± .XXX ± .XX ± ANGLES ±	POLYVINYL CHLORIDE	
R	09-20-16	JBN	MRJS	RGRO	RELEASED TO PRODUCTION	D34078CB-DC	THIRD ANGLE PROJECTION		D34078CB-DC
							DRAWN BY: JBN DATE: 09-20-16 CHK: MRJS SCALE: NONE		SHT 1 OF 1