


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART #	COLOR	A (REF) IN (mm)	B (REF) IN (mm)	C IN (mm)	APPROXIMATE WEIGHT LBS. (g)
PC20C13BL1.5	BLACK	0.30 (7.6)	3.07 (78)	18.1 (460)	0.18 (82)
PC20C13BL3				37.4 (950)	0.24 (111)
PC20C13BL6				72 (1830)	0.36 (165)



NOTES:

- SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- RATING: 10A/250V AC.
- CORD ASSEMBLY HAS THESE APPROVALS: VDE, CE, UL, CSA OR cUL.
- PRODUCT IS RoHS COMPLIANT.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	QC
OOA	7/19/12	DBLA	DJW	INITIAL DRAWING RELEASE	GAECN00095	OO	KLN		

CAD FILENAME/LAYERS		11K026BH_DC/00A	
<h1>PANDUIT</h1> CORP TINLEY PARK, ILLINOIS			
CUSTOMER DRAWING IEC60320-C20 TO IEC60320-C13 POWER CORD			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) $\pm$ .1 (.XXX) $\pm$ .005 (.XX) $\pm$ .01 ANGLES $\pm$ 5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY RVU	MAT'L:	SCALE	1 : 1
DATE 5/22/12	SEE NOTES	DRAWING NO.	DWG B
CHK'D KLN		11K026BH-DC	SIZE