



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
P24F06M-XYZ	SEE SHEET 2



LEFT VIEW




REAR VIEW




RIGHT VIEW

FOR LENGTH SEE SHEET 2 PART NUMBER TABLE.



FRONT VIEW

16 AMP, SINGLE - POLE ELECTRO MECHANICAL SWITCH / BREAKER (2) PLACES



BOTTOM VIEW

SPECIFICATION:


- STANDARD:
 - UNIT TYPE: MONITORED OUTLET
 - ORIENTATION: VERTICAL, 0U FULL
 - OUTLET QTY&TYPE: (20) C13, (4) C19
 - INPUT VOLTAGE: 200-240VAC
 - INPUT CURRENT: 32A
 - BREAKER QTY&TYPE: (2) 16AMP, SINGLE-POLE
 - INPUT PHASE: SINGLE-PHASE
 - RATED POWER: 7.4kVA
 - INPUT PLUG: IEC 60309 2P+E 6H 32A
 - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
 - REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL: NONE
- ACCESSORIES: (1) QUICK-START GUIDE

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24F06M-XX Y Z



PLUG/RECEPTACLE BLOCK



PLUG
IEC 60309, 2P 3W, 6H
IP44 (SPLASHPROOF)
32A, 200-250V MAX RATED INPUT



RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT



RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24F06M
01A	08/23/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24F06M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P24F06M-XYZ CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER: P24F06M_DC
DRAWN BY GEORGE	DATE 08/23/2017	CHK SEAN
SCALE NONE	SHT 1 OF 2	
		SCALE B

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24F06M	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-BL1A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-BL1B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-RD1A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-RD1B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-RD1C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-WH1A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-WH1B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-WH1C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-YL1A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-YL1B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-YL1C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-BU1A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-BU1B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-BU1C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-GN1A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-GN1B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-GN1C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-BL2A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-BL2B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-BL2C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-RD2A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-RD2B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-RD2C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-WH2A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-WH2B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-WH2C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-YL2A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-YL2B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-YL2C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-BU2A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-BU2B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-BU2C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg
P24F06M-GN2A	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'(+3.5'-1.75")	8.3kg
P24F06M-GN2B	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'(+7'-3.5")	8.6kg
P24F06M-GN2C	VERTICAL,(20) C13,(4) C19,MONITORED OUTLET , 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'(+10'-5")	8.9kg

B

B



A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY

SIGN _____
DATE _____
PRINT _____

TITLE
INTELLIGENT SERIES PDU
P24F06M-XYZ
CUSTOMER DRAWING

ITEM REVISION NAME:
DATASHEET FILE NAME:

UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]

Tolerance(mm)
0<L<50 ±0.5
50<L<250 ±1.0
250<L<500 ±1.5
500<L<1000 ±2.5
1000<L<2000 ±4.0

THIRD ANGLE PROJECTION

MATERIAL/COLOR:
N/A

DRAWING NUMBER:
P24F06M_DC

DRAWN BY: DATE: CHK: SCALE:
GEORGE 08/23/2017 SEAN NONE

SHT 2 OF 2 SCALE: B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24F06M
01A	08/23/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24F06M

2



1