



REFERENCE FULLY-CLOSED VIEW
(FRONT CKSB10-8)



REFERENCE FULLY-CLOSED VIEW
(SIDE CKSB10-8)



REFERENCE FULLY-CLOSED VIEW
(BACK CKSB10-8)

PANDUIT PART NUMBER	DIMENSIONS - IN [mm]			PACKAGE CONTAINS PANDUIT SPLIT BOLT PART NUMBER (PACKED INSIDE COVER)	PACKAGE CONTAINS PANDUIT INSULATING COVER PART NUMBER
	L	W	H		
CKSB10-8	2.40 [61.0]	1.12 [28.3]	1.70 [42.9]	SBC8-C	CVRSBC4
CKSB6-2	2.70 [67.4]	1.32 [33.5]	1.92 [48.8]	SBC2-C	CVRSBC2
CKSB1-00	3.10 [78.4]	1.55 [39.3]	2.40 [61.0]	SBC2/0-Q	CVRSBC2/0

NOTES:

- MATERIAL: PRODUCT PACKAGING CONTAINS SPLIT BOLT AND INSULATING COVER. SPLIT BOLT IS NESTED AND SHIPPED INSIDE THE INSULATING COVER. REFER TO TABLE FOR PANDUIT PART NUMBER CONTENTS.
- cULus LISTED to UL486A-B
- UL RATED FOR;
 - MAXIMUM OPERATING TEMPERATURE RATING: 90 deg C
 - MAXIMUM VOLTAGE RATING: 600V



PART NUMBER		CKSB10-8, CKSB6-2, CKSB1-00	
TITLE		PACKAGED SPLIT BOLT AND INSULATING COVER KIT CUSTOMER DRAWING	
ITEM REVISION NAME		-	
DATASET FILE NAME		-	
MATERIAL		see TABLE and NOTES	
DRAWN BY		DATE	CHK
BKA	01/10/2018	BKA	N/A
SCALE		N/A	
DRAWING NUMBER		00093FGE-DC	
SHEET 1 OF 1		B	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	8/20/2018	BKA	JBN	RGRO	RELEASE	038817