


Panduit® Fixed Diameter Cable Clamps

- Durable Nylon 6.6 cable clamps



Part Number	Max. Bundle Diameter A		Width B		Bundle Offset C		Mounting Method	Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	In.	mm	In.	mm			
CCS12-S8-C	0.12	3.1	0.37	9.4	0.33	8.4	#8 (M4) Screw	100	500
CCS19-S8-C	0.19	4.8	0.37	9.4	0.43	10.9			
CCS25-S8-C	0.25	6.3	0.37	9.4	0.41	10.4			
CCS25-S10-C	0.25	6.3	0.37	9.4	0.41	10.4	#10 (M5) Screw	100	500
CCS31-S8-C	0.31	7.9	0.37	9.4	0.49	12.4	#8 (M4) Screw	100	500
CCS38-S8-C	0.38	9.5	0.37	9.4	0.59	15.0			
CCS44-S8-C	0.44	11.1	0.37	9.4	0.57	14.5			
CCS50-S8-C	0.50	12.7	0.37	9.4	0.60	15.2			
CCH12-S10-C	0.12	3.1	0.50	12.7	0.36	9.1			
CCH19-S10-C	0.19	4.8	0.50	12.7	0.42	10.7	#10 (M5) Screw	100	500
CCH25-S10-C	0.25	6.3	0.50	12.7	0.46	11.7			
CCH31-S10-C	0.31	7.9	0.50	12.7	0.50	12.7			
CCH38-S10-C	0.38	9.5	0.50	12.7	0.53	13.5			
CCH44-S10-C	0.44	11.1	0.50	12.7	0.56	14.2			
CCH50-S10-C	0.50	12.7	0.50	12.7	0.59	15.0			
CCH56-S10-C	0.56	14.2	0.50	12.7	0.61	15.5			
CCH62-S10-C	0.62	15.7	0.50	12.7	0.65	16.5			
CCH69-S10-C	0.69	17.5	0.50	12.7	0.75	19.1			
CCH75-S10-C	0.75	19.1	0.50	12.7	0.78	19.8			
CCH81-S10-C	0.81	20.6	0.50	12.7	0.81	20.6			
CCH87-S10-C	0.87	22.1	0.50	12.7	0.84	21.3			
CCH100-S10-C	1.00	25.4	0.50	12.7	0.91	23.1			
CCH112-S10-C	1.12	28.4	0.50	12.7	0.97	24.6			
CCH119-S10-C	1.19	30.2	0.50	12.7	1.00	25.4			
CCH125-S10-C	1.25	31.8	0.50	12.7	1.06	26.9			
CCH138-S10-C	1.37	34.8	0.50	12.7	1.12	28.4			
CCH150-S10-C	1.50	38.1	0.50	12.7	1.19	30.2			

All parts listed are also available in black weather resistant material (add suffix 0). Bulk package only.