




RAIL KIT LEFT SIDE



RAIL KIT RIGHT SIDE



FRONT OF UPS IS ATTACHED TO THIS FLANGE

SPECIFICATION:

1. STANDARD:
USE WITH UPS CAPACITY: 1-20 KVA UPS AND EBP(UVP024/036/048/072/240)
DIMENSION RANGE: 469.5 ~ 996.8MM
2. ADDITIONAL:
RAILS ARE UNPAINTED
3. ACCESSORY COMPONENTS:
NUT M5*25 FOR RAIL KIT,QTY: (4)
FLOATING SCREWS M5 FOR RAIL KIT,QTY: (4)
INSTALLATION GUIDE FOR RAIL KIT,QTY: (1)
REFER TO ASSOCIATED DRAWINGS FOR PHYSICAL DIMENSIONS AND SPECIFICATIONS

NOTES:

1. PRIMARY DIMENSIONS ARE IN MILLIMETERS,SECONDARY DIMENSIONS ARE IN INCHES
2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL,STATE,AND LOCAL CODES
3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
4. ALL PURCHASED ITEMS CONFORM TO C2-0834 PANDUIT SPECIFICATION FOR CHEMICAL SUBSTANCES TO BE CONTROLLED IN PRODUCT AND PACKAGING

IDENTIFICATION:

PART NUMBER	DESCRIPTION	SHIPPING WEIGHT (KG)
URMKIT2	UPS RACK MOUNT RAIL KIT FOR 5-20KVA UPS	3.3

DIA 08/17/2021		D.L.	ZRZ	GM/D/B	UPDATED DESCRIPTION	URMKIT2	THIS DRAWING IS THE PROPERTY OF PANDUIT CORPORATION. IT IS TO BE USED ONLY FOR THE CLIENT'S SPECIFIC ORDER. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT EXPRESS WRITTEN PERMISSION FROM PANDUIT CORPORATION.	
DIA 08/17/2021		D.L.	ZRZ	GM/D/B	RELEASE TO PRODUCTION	URMKIT2	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: MM (IN)	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY: JEN DATE: 08/17/2021 D.W. CHECKED BY: JEN DATE: 08/17/2021 M.D. VARIOUS	PART NUMBER: URMKIT2-DC SHEET: 1 OF 2



N/A

URMKIT2-DC

SHT 1 OF 2