


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
FR4X4**2	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	7.80 LB (3538g)	1.19 LB/FT (17.7g/cm)
FR4X4**6	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	7.14 LB (3238g)	1.19 LB/FT (17.7g/cm)
FR4X4**3	118.11 IN ±.18 IN (3000mm ±4.6mm)	11.71 LB (5311g)	1.19 LB/FT (17.7g/cm)
FR4X4**10	120.00 IN ±.18 IN (3048mm ±4.6mm)	11.90 LB (5397g)	1.19 LB/FT (17.7g/cm)



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



D10100DA/14

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	5/11/2021	MES	PATR	PATR	ADDED PART NUMBERS FR4X4**3, FR4X4**10	V09002MM/00
3	02-20-13	JBN	RTFI	RN	G. UPDATED DRAWING BORDER & TITLE BLOCK	37847-46

TITLE FIBERRUNNER 4X4 CHANNEL (FR4X4**2, FR4X4**6, FR4X4**3, FR4X4**10) CUSTOMER DRAWING	
ITEM REVISION NAME D37847BA/02	
DATASET FILE NAME D37847BA_DC_FR4X4/02A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
.X ± .XX ± .03 [.8]	.XXX ± ANGLES ±
THIRD ANGLE PROJECTION	
DRAWN BY JHNU	DATE 07-13-01
CHK DJWA	SCALE NONE
MATERIAL: PVC	
DRAWING NUMBER: 37847-46	
SHT 1 OF 1	
SIZE A	

2

1