


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [] ARE METRIC.
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
4. LABEL COLOR IS WHITE.
5. WORKS WITH PTM-C3500 PRINTER.

PART NO.	"A" INCH	"B" INCH	LENGTH FOOT [M]	MATERIAL	LABEL MATERIAL	ADHESIVE
T200X000WJI	2.00 [50.8]	2.20 [55.9]	30 [9.14]	GMV19-R	VINYL	STANDARD
T200X000WJI -B	2.00 [50.8]	2.20 [55.9]	100 [30.48]	GMV19-R	VINYL	STANDARD
T400X000WJI	4.00 [101.6]	4.20 [106.7]	30 [9.14]	GMV19-R	VINYL	STANDARD
T400X000WJI -B	4.00 [101.6]	4.20 [106.7]	100 [30.48]	GMV19-R	VINYL	STANDARD
T200X000XJI	2.00 [50.8]	2.20 [55.9]	30 [9.14]	GMV10-R	POLYESTER	STANDARD
T400X000XJI	4.00 [101.6]	4.20 [106.7]	30 [9.14]	GMV10-R	POLYESTER	STANDARD
T200X000XPI	2.00 [50.8]	2.20 [55.9]	30 [9.14]	GMV10-S	POLYESTER	SUPERTACK
T400X000XPI	4.00 [101.6]	4.20 [106.7]	30 [9.14]	GMV10-S	POLYESTER	SUPERTACK

PART NUMBER		SEE TABLE	
TITLE			
CONTINUOUS TAPE FOR INK JET PRINTERS			
CUSTOMER DRAWING			
ITEM REVISION NAME		00211EBU/00	
DATASET FILE NAME		00211EBU_DC/00A	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE TABLE	
DRAWING NUMBER		00211EBU_DC	
REV	DATE	BY	CHK
00A	10/26/20	ACC	DBLA
REV	DATE	BY	CHK
00A	10/26/20	ACC	DBLA

A-SIZE CUSTOMER

00A	10/26/20	ACC	DBLA	RCMC	INITIAL RELEASE	089515
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/26/20	ACC	DBLA	RCMC	INITIAL RELEASE	089515
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN