

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2

SPECIFICATION:


- STANDARD
 UNIT TYPE: MONITORED SWITCHED
 ORIENTATION: VERTICAL, 0U FULL
 OUTLET QTY & TYPE: (18)C13, (6)C19
 INPUT VOLTAGE: 200-240/346-415VAC
 INPUT FREQUENCY: 50/60HZ
 INPUT CURRENT: 32A
 BREAKER QTY & TYPE: (6)16AMP, SINGLE-POLE
 INPUT PHASE: THREE-PHASE (WYE)
 RATED POWER: 22KVA
 INPUT PLUG: IEC 60309 3P+N+E 6H 32A
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
 REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL:
 NONE
- ACCESSORIES:
 DOCUMENTATION KIT
 PRODUCT SAFETY WARNING SHEET

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION:

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E24E03M-XXYZ



WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____
 DATE _____
 PRINT _____

TITLE: **INTELLIGENT SERIES PDU E24E03M**
 CONTROL DRAWING

ITEM REVISION NAME: _____
 DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED
 DIMENSIONAL TOLERANCE ARE: mm [IN]
 Tolerance (mm)
 0 < L ≤ 50 ± 0.5
 50 < L ≤ 250 ± 1.0
 250 < L ≤ 500 ± 1.5
 500 < L ≤ 1000 ± 2.5
 1000 < L ≤ 2000 ± 4.0


MATERIAL / COLOR: N/A

DRAWING NUMBER: **E24E03M_DC**

THIRD ANGLE PROJECTION

DRAWN BY: LL DATE: 08/29/2023 CHK: MIM SCALE: NONE

SHT 1 OF 2 SCALE: B



PLUG / RECEPTACLE BLOCK

PLUG
 IEC 60309 3P+N+E 6H
 IP44 (SPLASHPROOF)
 32A, 346-415V MAX RATED INPUT

RECEPTACLE
 IEC 60320 C13
 10A, 250V MAX RATED OUTPUT



RECEPTACLE
 IEC 60320 C19
 16A, 250V MAX RATED OUTPUT

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24E03M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E24E03M	MS PDU, 32A, (18)C13 (6)C19, IEC 60309 3P+N+E 6h IP44-3M, TOP-FED, BLACK	BLACK(RAL 9005)	3M(+254MM/-127MM)[10'(+10"/-5")]	8.4kg

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24E03M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU E24E03M CONTROL DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance (mm) 0 < L ≤ 50 ±0.5 50 < L ≤ 250 ±1.0 250 < L ≤ 500 ±1.5 500 < L ≤ 1000 ±2.5 1000 < L ≤ 2000 ±4.0		N/A
 THIRD ANGLE PROJECTION		DRAWING NUMBER:
DRAWN BY: LL DATE: 08/29/2023		E24E03M_DC
CHK: MIM	SCALE: NONE	SHT 2 OF 2
		SCALE: B