



Optimally Equipped Conference Rooms Enable and Enhance Collaboration

Conference rooms in a digital building can be one of the busiest places in the building. Teams – each with different needs – cycle through throughout the day, sharing ideas, solving problems, brainstorming the next big idea. When properly equipped, the room contributes to that collaboration:

- AV equipment connects seamlessly
- Sensors detect occupancy and HVAC adjusts to maintain temperatures and ventilation
- Lights adjust automatically to support the activity in the room
- Calendar integration alerts users when a room is open, or when a meeting time is ending

The right infrastructure enables the systems that enhance collaboration, communication, and productivity. Atlona's wide range of AV devices mean you can equip your rooms with the exact AV features you need, including systems that allow touch-free wireless connection from any device, and USB ports for easy connection of cameras, audio systems, and other peripherals to collaborate with remote audiences. Simple, reliable operation allows participants to focus on the topic – not the equipment.

Panduit infrastructure connects the AV system, wireless access points, PoE lighting, and more, with the robust, reliable performance that you expect from Panduit. Enhance the collaboration and productivity of your conference rooms with Panduit solutions.



Part Number	Part Description
-------------	------------------

Atlona Products

AT-OME-MS52W	5x2 MaTriX switcher with USB and wireless presentation link.
AT-HDVS-CAM	Pan-tilt-zoom camera with USB.
AT-OME-EX-RX	HDBaseT receiver for HDMI with USB.
AT-VGW-HW	Gateway for AV control and management plus room scheduling.
AT-VSP-800	Velocity system 8-inch scheduling touch panel for room scheduling and AV control.

Horizontal Cable

PUP6AHD04BU-G	Category 6A Vari-MaTriX High Density U/UTP copper cable, plenum, 4-pair, Blue.
----------------------	--

Jack Modules and Modular Plugs

FC-ICCP1MBU	TX6A™ Category 6A UTP FieldCord™ Connector for field termination of 4-pair UTP cable to connect devices with confined port spaces.
FP6X88MTG	TX6A™ Category 6A Field Term Plug for field termination of 4-pair UTP cable. Compatible with Category 6A, Category 6, and Category 5e systems.
FPU6X88MTG	TX6A™ Category 6A Field Term Plug with up-down angled wire cap for field termination of 4-pair UTP cable. Compatible with Category 6A, Category 6, and Category 5e systems.
CJ6X88TGBU	Category 6A, RJ45, 8-position, 8-wire universal jack module with MaTriX Technology, Blue. Supports high-bandwidth applications and is ideal for running next generation Power over Ethernet (PoE++). UL Rated: UL 1863 and UL 2043.
CJUDCAPBU-C	Category 6A 45° angled up/down TG wire cap provides improved cable routing to jacks in confined spaces; 100 pk.

Patch Cords

UTP28X7BL	Category 6A performance, 28 AWG, UTP patch cord, CM/LSZH, 7 ft., Blue.
AT-LC-H2H-1M	Atlona LinkConnect™ H2H High Speed HDMI to HDMI cable for reliable, consistent AV performance; 1 meter; Black. (Available through Atlona.)

Above Floor Raceway

AFR4BCBL6	Above floor raceway base and cover, 6 ft., Black. Compatible with a wide range of fittings, couplers, and junction boxes.
AFR4TBLGBL	Above floor raceway table leg fitting to route cable to a desktop or table top, Black.

See www.panduit.com for additional colors, sizes, cable jackets, and performance offerings.

