



Best-in-Class Outlet Density

---

Optimal Form Factors

---

Superior Reliability

---

**G6**


---

**Security and Environmental  
Monitoring Solutions with  
Panduit® G6 iPDU Solution**

**PANDUIT®**

# Security Solution

- iPDUs (intelligent pdu series: Metered Input, Metered per Outlet, Metered, and Switched, Metered and Switched per Outlet)
- G6 Security Handle with Dual Freq Card Reader (ACF05) or G6 Security Handle with Dual Freq Card Reader and Keypad enabling Dual Authentication (ACF06)
- Cable Harness (ACF20) that connects the G6 Security Handle to the G6 iPDU
- Recommend using MA030 extension cord and coupler enabling cabinet door removal via quick disconnect
- Recommend using ACA01 door contact sensor to enable physical sensing of door position



\*A maximum of 200 HID Cards can be managed

\*\*The MA030 features a coupler to optimize door removal and is 10 ft. (3 m) in length

# Environmental Solution

- iPDUs (intelligent pdu series: Metered Input, Metered per Outlet, Metered and Switched, Metered and Switched per Outlet)
- 3-way Temperature & Humidity Sensor (EC001), in the front door
- Temperature Sensor (EA001), in the rear door

FRONT OF CABINET  
(COLD AISLE SIDE)

3 Temperature and  
1 Humidity Sensor - EC001



REAR OF CABINET  
(HOT AISLE SIDE)


Panduit® iPDU  
(MI, MS, MPO, or MSPO series)

Temperature Sensor - EA001



# Security and Environmental Solution

- iPDUs (intelligent pdu series: Metered Input, Metered per Outlet, Metered and Switched, Metered and Switched per Outlet)
- G6 Security Handle with Dual Freq Card Reader (ACF05) or G6 Security Handle with Dual Freq Card Reader and Keypad enabling Dual Authentication (ACF06)
- Cable Harness (ACF20) that connects the G6 Security Handle to the G6 iPDU
- Recommend using MA030 extension cord and coupler enabling cabinet door removal via quick disconnect
- Recommend using ACA01 door contact sensor to enable physical sensing of door position



\*A maximum of 200 HID Cards can be managed

\*\*The MA030 features a coupler to optimize door removal and is 10 ft. (3 m) in length

Complete Warranty & Compliance information can be found at [www.panduit.com](http://www.panduit.com)  
 Customer Service: [cs@panduit.com](mailto:cs@panduit.com) or 800.777.3300  
 Technical Support: [techsupport@panduit.com](mailto:techsupport@panduit.com) or 866.405.6654