




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





VIEW ROTATED 180°



- STANDARD:
USE WITH UPS CAPACITY: 5-10 KVA SINGLE PHASE UNIT
BATTERY TYPE: LITHIUM-ION
NOMINAL INPUT/OUTPUT VOLTAGE: 192VDC
BREAKER TYPE: 63A/2P(1)
- ADDITIONAL:
NONE
- ACCESSORY COMPONENTS:
STABILIZER BRACKET, QTY: (4)
INSTALLATION EARS, QTY: (2)
PRODUCT SAFETY WARNING SHEET, QTY(1)
BATTERY CONNECTOR SECURING BRACKET, QTY, (2)
M3 FLANGE NUT, QTY, (4)
M3X20 SCREW, QTY, (4)
EBC POWER CABLE, QTY, (1)
EBC COMMUNICATION CABLE, QTY, (1)
R145 COMMUNICATION CABLE, QTY, (2)
INCLUDES P/N:URMKIT2 INSTALLATION RAIL KIT, QTY (1)
DOCUMENTATION KIT, QTY(1) - TO BE PLACED ON TOP OF ALL PACKAGING MATERIAL
REFER TO ASSOCIATED DRAWINGS FOR PHYSICAL DIMENSIONS AND SPECIFICATIONS



DETAIL A
SCALE 1:2



- NOTES:
- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN INCHES
 - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
 - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PRODUCT.
 - ALL PURCHASED ITEMS CONFORM TO C2-0834 BANDUIT SPECIFICATION FOR CHEMICAL SUBSTANCES TO BE CONTROLLED IN PRODUCT AND PACKAGING

| IDENTIFICATION: | DESCRIPTION | SHIPPING WEIGHT (KG) |
|------------------------|---|----------------------|
| PART NUMBER UVPL12H | LFP LITHIUM EXTERNAL BATTERY PACK (EBP) 4*60P-CS 50 AMPERS CHARGES, AND RAIL KIT INCLUDED, FOR 5, 6, 10KVA UPS ONLY | 39.9 |

| REV | DATE | BY | CHK | APP | DESCRIPTION | ECN | DATE | USER | STATUS |
|-----|------------|-----|---------|-----|-----------------------|-----|------------|------|---------|
| 001 | 10/2023 | MDH | SAU/MDH | | RELEASE TO PRODUCTION | | | | |
| 002 | 10/18/2023 | MDH | | | IMB ASSE | | 10/18/2023 | MDH | VARIOUS |

| REV | DATE | BY | CHK | APP | DESCRIPTION | ECN | DATE | USER | STATUS |
|-----|------------|-----|-----|-----|----------------------------------|-----|------|------|--------|
| 001 | 10/18/2023 | MDH | | | EXTERNAL BATTERY PACK UVPL12H | | | | |
| 002 | 10/18/2023 | MDH | | | CONTROL DRAWING | | | | |
| 003 | 10/18/2023 | MDH | | | UVPL12H /00 | | | | |
| 004 | 10/18/2023 | MDH | | | UVPL12H /00A | | | | |
| 005 | 10/18/2023 | MDH | | | UNLICENSED RESOURCES PART 10 (N) | | | | |

| REV | DATE | BY | CHK | APP | DESCRIPTION | ECN | DATE | USER | STATUS |
|-----|------------|-----|-----|-----|----------------------------------|-----|------|------|--------|
| 001 | 10/18/2023 | MDH | | | EXTERNAL BATTERY PACK UVPL12H | | | | |
| 002 | 10/18/2023 | MDH | | | CONTROL DRAWING | | | | |
| 003 | 10/18/2023 | MDH | | | UVPL12H /00 | | | | |
| 004 | 10/18/2023 | MDH | | | UVPL12H /00A | | | | |
| 005 | 10/18/2023 | MDH | | | UNLICENSED RESOURCES PART 10 (N) | | | | |

