


## SPECIFICATIONS

The FlexCore Universal Patch Panel 4 RU shall house, organize, manage, and protect optic cable, terminations, cassettes, connectors, and patch cords. The Universal Patch Panel's ambidextrous design allows cables and/or patch cords to exit either left or right when used with the corresponding cassettes, frames and accessories.

The Universal Patch Panel includes mounting brackets and identification labels for connector ports and trays.



## KEY FEATURES AND BENEFITS

<b>Modular design</b>	Provides high field density with 288 fiber connections (12 × 24 fiber cassettes per enclosure) or 288 fiber/576 fiber connections (discrete splice/ribbon cable-cable splice) maximizing valuable rack space
<b>Compatible with front-facing fiber cassettes</b>	Provides versatility and flexibility with a fully modular solution for a variety of pre-terminated or field terminated installations. Adjustable rail system supports multiple form factor cassettes.
<b>Front-facing patch panel</b>	Allows easy front access to connections with no moving parts, facilitating easy moves, adds and changes without disruption
<b>Optional lock kit for enhanced security</b>	Provides security to prevent unauthorized access (sold separately)

## GENERAL SPECIFICATIONS

<b>Access</b>	Front
<b>Color</b>	Gray or Black
<b>Configuration</b>	Unloaded
<b>Mounting:</b>	FlexCore Frame

## DIMENSIONS

Dimension:	Part Number	RU	Height In. (mm)	Width In. (mm)	Depth In. (mm)
	<b>FDFUPN4GY</b>	4	6.9 (172.5 mm)	17.35 (441 mm)	11.38 (289 mm)

NOTE: For part number in black, replace GY with BL


## MATERIAL SPECIFICATIONS

<b>Finish</b>	Powder coated
<b>Material type</b>	Steel
<b>Accessories</b>	Molded plastic

## ENVIRONMENTAL SPECIFICATIONS

<b>Environment</b>	Indoor
<b>Standards</b>	RoHS

# FlexCore™ Universal Patch Panel 4 RU



Patch Panel Gray with no cover



Patch Panel with 12 fixed trays

Panduit Patent US 1072528: Modular Fiber Tray

## WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

**PANDUIT**®

For more information  
**Visit us at [www.panduit.com](http://www.panduit.com)**  
Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

© 2024 Panduit Corp.  
ALL RIGHTS RESERVED.  
RKSP213-WW-ENG  
5/2024