

Strain Relief Bars

Strain relief bars are used to support and manage cables in telecommunication rooms. Design ranges from a simple straight bar to one with distinctive features such as integrated adjustable clips or one that pivots up and down for easier access. All strain relief bars include mounting hardware and are available in black color. Optional hardware kits allow mounting the strain relief bars onto single cage nut or threaded rails to provide a location to securely mount behind the patch panel.

Straight Design

- Ideal for use in 2-post racks. For single rail installations the Quick Release bracket is recommended.

Part Number	Description
SRBS19BL-XY	Basic straight bar comes in a bulk package of 10 to reduce single-use plastic
SRBWCY	Offers integrated adjustable clips to help organize 24 cables individually, with easy release mounting feature
SRBM19BLY	Cascading contoured surface with raised tie mounts, includes 6 Tak-Ty® Hook & Loop Cable ties to help secure and manage cables, with easy release mounting feature



SRBS19BL-XY



SRBWCY



SRBM19BLY

Extended Design

Outward mounting tabs

Part Number	Description
SRB19BLY	Extends 2.8 in. off the rack
SRB19ED5BL	Extends 4.5 in. off the rack
SRB19ED7BL	Extends 7.5 in. off the rack, ideal for installations with cable assemblies that require additional depth
SRB19MDBL	Extends 7.5 in. off the rack, includes two cross bars to help support heavier cables




SRB19BLY



SRB19ED5BL



SRB19ED7BL



SRB19MDBL

Inward mounting tabs

- Mounting tabs are inward to provide additional clearance. Require 19.75" clearance between rails.

Part Number	Description
SRB19D5BL	Extends 4.5 in. off the rack
SRB19D7BL	Extends 7.6 in. off the rack, includes one crossbar to help support heavier cables



SRB19D5BL



SRB19D7BL

Specialty Designs

- Strain relief bars with unique features that provide easy access to the connections.

Part Number	Description
SRBPBL	Pivoting strain relief bar, features a rear flange to help manage and support cables. Includes up and down swivel motion to allow easy access to connections
SRBPPQBRKT	Features a rear flange, with quick release feature, mounts directly behind Panduit patch panels, ideal for single rail applications, includes cable ties



SRBPBL



SRBPPQBRKT

Accessories

- Provide an alternative way to mount Panduit's extensive line of strain relief bars.

Part Number	Description
SRBBRKT	Quick Release Bracket. Allows strain relief bars to be removed and re-installed without the use of tools
CNSRBKIT-C	Cage Nut Mounting Hardware. Allows mounting strain relief bars to single rails where cage nuts are required
TRSRBKIT-C	Threaded Mounting Hardware. Allows mounting strain relief bars to single rails with threaded holes



SRBBRKT



CNSRBKIT-C



TRSRBKIT-C

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

© 2024 Panduit Corp.
ALL RIGHTS RESERVED.
RKSG13-WW-ENG
6/2024