



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

1.44" [37] CT-2525CH, CT-2550CH & CT-2500CH (WITH LOCATOR)  
 1.25" [32] CT-2570CH (WITHOUT LOCATOR)



**NOTES, UNLESS OTHERWISE SPECIFIED:**

The CT-2500 and CT-2500/E Battery Operated Crimping Tools are designed to crimp #10 AWG thru #22 AWG PANDUIT terminals, disconnects and splices.

The CT-2500 and CT-2500/E Tools include:

- 1 – Battery Operated Crimping Tool (with battery cartridge)
- 1 – Spare Battery Cartridge
- 1 – Battery Charger
- 1 – Tool Case

Weight (including battery) 3.3 lbs. (1,5 kg)  
 Dimensions: 11-3/4" L x 2-3/8" H x 3-1/8" W – with battery  
 [298 L x 60 H x 80 W] mm  
 Crimping Time 2 seconds  
 Crimping Force 1.7 tons (15 kN)

CT-2500 and CT-2500/E Battery Operated Crimping Tools are to be used with optional Crimping Heads: CT-2525CH, CT-2550CH and CT-2500CH, which are supplied with locator (for insulated); and CT-2570CH (for non-insulated), and are sold separately.

The CT-2500CH Crimping Head (frame only) is used with optional Crimping Die Inserts: CD-525, CD-550 and CD-570, which are sold separately.

The operation manual for the CT-2500 and CT-2500/E tools, plus optional crimping heads and die inserts can be found at: [www.panduit.com](http://www.panduit.com).

Replacement Batteries and Battery Chargers are sold separately.

- CT-2500BC Replacement Battery Cartridge
- CT-2500CHR Replacement Battery Charger
- CT-2500CHR/E Replacement Battery Charger for Europe

Dimensions in [brackets] are in millimeters.  
 All dimensions are for reference only.

F:\wrkgrp\rvusers\ENGR DOCS-NEW\CUSTOMER DRAWINGS\TP25386B01\_02 CT-2500\_CT-2500-E CD.doc

CT-2500 TOOL BODY SHOWN WITH CT-2525CH CRIMPING HEAD ATTACHED

REV	DATE	BY	CHK'D	DESCRIPTION	ECN	- R	CUST	SUP
02	4-04-08	BLR	BJPU	ADD CT-2500CH & DIE INSERT INFO	4290	---	JRWA	
01	8-01-07	BLR	SRRE	UPD GRAPHIC W/LED	4241	---	JRWA	
00	3-02-07	BLR	SRRE	RELEASED	4241	---	SZ	

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

**CD\*CT-2500 & CT-2500/E**

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
 (.x) ± --- (.xxx) ± ---  
 (.xx) ± --- ANGLES ± ---

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: **BLR** MATL: -----  
 DATE: **3-02-07**  
 CHK'D: **SRRE**

SCALE: **NONE**  
 DRAWING NO. **TP25386B01** DWG SIZE **B**