



Pan-Term® F80-15-M Non-covered Ferrules

F80-15-M

Ferrule, non-insulated, 14 AWG wire range, 0.59(15.0mm) length.

Specifications

Ferrule Type	Single Wire Standard
Copper Conductor Size (AWG)	#14
Maximum Copper Conductor Size (AWG)	#14
Maximum Metric Conductor Size (mm ²)	2.5
Minimum Copper Conductor Size (AWG)	#14
UL Temperature Rating (°C)	150
CSA Temperature Rating (°C)	150
Wire Strip Length (In.)	19/32
Wire Strip Length (mm)	15
Inside Diameter (In.)	0.09
Inside Diameter (mm)	2.2
Maximum Operating Temperature (°C)	150
Maximum Operating Temperature (°F)	302
Outer Diameter (In.)	0.1
Outer Diameter (mm)	2.5
Overall Length (In.)	0.59
Overall Length (mm)	15
Product Type	Non-Covered Ferrule
Standards Met	DIN 46228, CSA C22.2 No. 291-14, UL 486F, cULus 486F
Finish/Coating	Tin-Plated
For Use With	CT-1002, CT-1003, CT-1123, CT-1090, CT-1160, CT-1170, CT-2300/ST (CD-090), CT-2500/L (CT-2523CH)
Packaging Type	Bag
Base Material	Copper
Color Code	Metallic
Sub Brand	Pan-Term®
Part Features	Designed with a seamless barrel to contain loose wire strands for superior terminations Eases insertion of wire into terminal block Meets DIN, UL & CSA standards for wire containment Suitable for limited space panel

Packaging Detail

UPC	07498376339
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.0082
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000