



2-Post Rack, 42RU, #12-24 Threaded E-Rails, Aluminum, Black

R2P79

The 2-Post rack provides a reliable foundation for mounting telecommunications and data center equipment. The 79 inch tall rack accepts 19-inch wide equipment with mounting rails that have #12-24 EIA universal mounting hole spacing, and printed numbering from the bottom up. A range of cable managers and accessories work with the rack. The 3-inch deep channel rack is UL listed for 1,000 pounds and is made of extruded aluminum. The rack is 42 RU and black.

Specifications

| | |
|---------------------------|--|
| Note | Rack channel depth is 3" (76mm) |
| Material | Aluminum |
| Mounting Bolt Method | Threaded |
| Extended Depth (In.) | 15 |
| Extended Depth (mm) | 381 |
| Overall Width (In.) | 20.3 |
| Overall Width (mm) | 516 |
| Extended Height (In.) | 79 |
| Extended Height (mm) | 2.007 |
| Number of Rack Units | 42 |
| Mounting Hole Thread Size | #12-24 |
| Rail Number Direction | Bottom Up |
| Static Load Capacity (kg) | 454 |
| Static Load Capacity (lb) | 1000 |
| Color | Black |
| Standards Met | UL 2416, EIA/ECA-310-E, RoHS Compliant |
| Includes | (12) 3/8-16 x 1" hex head cap screw, (12) 3/8-16 hex nuts, (24) 3/8" paint piercing grounding washer, (1) tube of anti-oxidizing paste, (24) 12-24 x .5" slotted pan head steel screws |
| Product Type | 2-Post Rack |
| Finish/Coating | Powder-Coated |
| Part Features | Rails Numbered Bottom Up |

Packaging Detail

| | |
|-----------------------|-------------|
| UPC | 07498331235 |
| Std. Pkg. Qty. | 1 |
| Std. Pkg. Volume (cf) | 1.2415 |
| Std. Ctn. Qty. | 0 |
| Std. Ctn. Volume (cf) | 0.0000 |