



## Dry-Shrink™ HSTT75-48-545 Heat Shrink

HSTT75-48-545

The HSTT75-48-545 Thin Wall Heat Shrink Tubing shrinks around wires, connectors, joints, and terminals when heated to protect against abrasion. Applications include insulating and protecting wires/cables in indoor, dry locations. Shrink ratio: 3:1. Temperature range: -67°F to 275°F (-55°C to 135°C). Flame retardant, cross-linked polyolefin. .75" (19.0mm) Diameter, Color: Yellow/Green, 5 pc. per pkg.

### Specifications

Product Type	Heat Shrink Tubing
Adhesive Lined	No
Color	Yellow/Green
Material	Cross-Linked Polyolefin
Maximum Operating Temperature (°C)	135
Maximum Operating Temperature (°F)	275
Minimum Operating Temperature (°C)	-55
Minimum Operating Temperature (°F)	-67
Nominal Diameter (In.)	0.75
Nominal Diameter (mm)	19.1
Nominal Recovered Wall Thickness (In.)	0.03
Nominal Recovered Wall Thickness (mm)	0.8
Sub Brand	Dry-Shrink™
Overall Length (In.)	48
Overall Length (ft.)	4
Overall Length (m)	1.2
Overall Length (mm)	1219
Resistance Properties	Flame-Retardant
Standards Met	UL Recognized, CSA Approved, MIL SPEC
Shrink Ratio	3:1
Shrink Temperature (°C)	90
Shrink Temperature (°F)	194
Maximum Recovered Inside Diameter (In.)	0.375
Maximum Recovered Inside Diameter (mm)	9.5
Minimum Expanded Inside Diameter (In.)	0.75
Minimum Expanded Inside Diameter (mm)	19.1
Application	For Dry Locations

**Packaging Detail**

UPC	07498352064
Std. Pkg. Qty.	5
Std. Pkg. Volume (cf)	0.1950
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000