

Lithium Battery Parameters

REGULATION (EU) 2023/1542 Article 10 - Annex IV of Part A Performance and durability requirements		
Model : UVPL12H - 192V Lithium-Ion EBP		
Sl no.	Parameter	Value
1	Rated capacity (in Ah)	12Ah
2	Rated capacity fade (in %)	4.8Ah(40% to EOL)
3	Power (in Wh)	6648.962W (which is composed of 60 pcs LFP cells of 3.2V/3Ah connected in series and 4pcs LFP cells of 3.2V/3Ah connected in parallel, and consist of 60S4P pack)
4	Power fade (in %)	6441.645W(40% to EOL)
5	Internal resistance (in Ω)	$\leq 0.180\Omega$
6	Internal resistance increase (in %)	$\leq 100\%$
7	Where applicable, energy round trip efficiency	93%
8	Where applicable, energy round trip efficiency fade (in %)	90%
9	Expected life-time of the battery	5 Years

REGULATION (EU) 2023/1542 ANNEX VII	
PARAMETERS FOR DETERMINING THE STATE OF HEALTH AND EXPECTED LIFETIME OF BATTERIES	
Model: UVPL12H - 192V Lithium-Ion EBP	
Part A : Parameters for determining the state of health of stationary battery energy storage systems	
Parameter	Value
The remaining capacity	12Ah (initial Value)
Where possible, the remaining power capability	2304Wh (initial Value)
Where possible, the remaining round-trip efficiency	93% (initial Value)
The evolution of self-discharging rates	0.8%/hour
where possible, the ohmic resistance	<180 mOHM (initial Value)

REGULATION (EU) 2023/1542 ANNEX VII	
PARAMETERS FOR DETERMINING THE STATE OF HEALTH AND EXPECTED LIFETIME OF BATTERIES	
Model: UVPL12H - 192V Lithium-Ion EBP	
Part B Parameters for determining the expected lifetime of stationary battery energy storage systems	
Parameter	Value
The date of manufacture of the battery and, where appropriate, the date of putting into service	View product label
The energy throughput	2304Wh (initial Value)
The capacity throughput	93% (initial Value)
The tracking of harmful events such as: (below items)	
(a)the number of deep discharge events	0 (initial value)
(b)time spent in extreme temperatures	0 (initial value)
(c)time spent charging in extreme temperatures	0 (initial value)
The number of full equivalent charge discharge cycles	0 (initial value)