



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| FINISHED GOOD PART NUMBER | FINISHED GOOD DESCRIPTION | COLOR | INPUT CORD LENGTH | WEIGHT |
|---------------------------|---|------------------|--------------------------------|--------|
| P24D24G | G6 MI PDU,16AMP, (20) C13 (4) C19, NEMA L6-20P-3M, TOP FED, BLACK | BLACK (RAL 9005) | 3M(+254MM-127MM) 10'[+10"/-5"] | 7.2kg |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |

B

B

A

A

| | | | | | | | | | | | |
|-----|------------|----|-----|-----|--|--------------|------------------------|------------|------------------------------------|-----------------|-----------------|
| | | | | | WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY | | | | | SIGN | |
| | | | | | | | | | | DATE | |
| | | | | | | | | | | PRINT | |
| | | | | | TITLE INTELLIGENT SERIES PDU P24D24G-XXYZ CUSTOMER DRAWING | | | | | | |
| | | | | | ITEM REVISION NAME | | | | | | |
| | | | | | DATASHEET FILE NAME: | | | | | | |
| | | | | | UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN] | | | | | MATERIAL/COLOR: | |
| | | | | | Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0 | | | | | N/A | |
| 00A | 09/21/2023 | NW | CSH | MJD | INITIAL RELEASE | P24D24G-XXYZ | THIRD ANGLE PROJECTION | | DRAWING NUMBER: P24D24G-XXYZ_DC | | |
| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN | DRAWN BY | DATE | CHK | SCALE | SCALE |
| | | | | | | | NW | 08/30/2023 | CSH | NONE | SHT 2 OF 2 B |

