

Spiral Wrap

Looking to bundle and protect multiple wires or cables? Spiral Wrap harnesses numerous cables into a single manageable bundle while still allowing for breakouts of single or multiple cables. The wraps provide excellent abrasion protection for wires, cables, hoses, and tubing. Plus, the various colors allow for quick and easy identification of cable bundles. Spiral Wrap is offered in various bundle diameter ranges and lengths to solve a broad range of bundling needs.



- Installation tool supplied in each package
- Available in multiple materials
- Reusable
- UL File: E141152
- Voltage Rating: 600V

Part Number	Material*	Color	Length Per Reel‡		Bundle Diameter Range		Outside Diameter		Temperature Range	Wall Thickness		Std. Pkg. Qty.
			Ft.	m	In.	mm	In.	mm		In.	mm	
T25F-C	Polyethylene	Natural	100	30.5	3/16 – 2	4.8 – 50.8	0.25	6.4	-40°F – 122°F (-40°C – 50°C)	0.040	1.02	1
T38F-C					5/16 – 3	7.9 – 76.2	0.38	9.5		0.055	1.40	
T50F-C		Yellow			3/8 – 4	9.5 – 101.6	0.50	12.7		0.060	1.52	
T50F-C4Y												
T50F-C0	Weather Resistant Polyethylene											
T25T-L	TFE^	Natural	50	15.2	3/16 – 2	4.8 – 50.8	0.25	6.4	-454°F – 356°F (-270°C – 180°C)	0.030	0.76	
T50T-Q			25	7.6	3/8 – 4	9.5 – 101.6	0.50	12.7				

*Flame retardant products are manufactured from a material that is rated UL 94V-0.




‡Reel packaging may contain splices. Contact Panduit Customer Service for further information.

^TFE is Polytetrafluorethylene material.

Grommet Edging

Polyethylene Slotted Grommet Edging is the best solution for protecting wires and cables from chafing against panel walls and knockouts' sharp edges. This Grommet Edging features slots specifically designed for use on irregularly shaped and round panel holes. The polyethylene material is highly flexible, while the adhesive lining ensures the product will stay in place. Packaged on a 100' (30.5m) reel for easy handling and dispensing.

- Use slotted product on irregularly shaped and round panel holes
- Provided in 0.030" (0.8mm) thick material making it highly flexible
- Adhesive Lined Grommet Edging: 3 year shelf life



Part Number	Width A		Height B		Panel Thickness Range		Material	Color	Temperature Range	Std. Pkg. Qty.
	In.	mm	In.	mm	In.	mm				

Slotted Adhesive Lined

GEE62F-A-C	0.13	3.3	0.16	4.1	0.036 – 0.062	0.9 – 1.6	Polyethylene	Natural*	-40°F – 122°F (-40°C – 50°C)	1
GEE99F-A-C	0.17	4.3	0.19	4.7	0.062 – 0.099	1.6 – 2.5				
GEE144F-A-C	0.21	5.4	0.22	5.6	0.099 – 0.144	2.5 – 3.7				

*Natural color can range from opaque to clear.

UL® SP® Braided Expandable Sleeving – Polyethylene Terephthalate (PET)

PET Braided Expandable Sleeving provides continuous abrasion resistance and lightweight, durable protection, with a flexible open weave that will not trap heat or humidity. The flexible design also allows for use with irregular shapes.

- Compliant with U.S. and European passenger rail standards
- Rated for use up to 257°F (125°C)
- UL: E116868
- CSA: 227630



Part Number	Color	Nominal I.D.		Nominal Diameter Range		Length per Reel‡		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm	Ft.	m		
SE50P-DR0	Black	0.50	12.7	0.250 – 0.750	6.4 – 19.1	500	152.4	1	2

‡Reel packaging may contain splices. Contact Panduit Customer Service for further information.

UL® SP® Braided Expandable Sleeving – Flame Retardant Polyethylene Terephthalate

PET Flame Retardant Braided Expandable Sleeving provides all the same protection and flexibility of the standard PET Sleeving but with a flammability rating that meets UI 1441 VW-1.

- Compliant with U.S. and European passenger rail standards
- Rated for use up to 257°F (125°C)
- Flammability: Meets UL 1441 VW-1
- UL E116868
- CSA: 227630



Part Number	Color	Nominal I.D.		Nominal Diameter Range		Length per Reel‡		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm	Ft.	m		
SE50PFR-DR0	Black	0.50	12.7	0.250 – 0.750	6.4 – 19.1	500	152.4	1	2

‡Reel packaging may contain splices. Contact Panduit Customer Service for further information.

Corrugated Loom Tubing

Corrugated Loom Tubing is an economical solution for cables in wire harness applications. Polypropylene tubing provides light crush/impact resistance and is abrasion-resistant to reduce the risk of damage to wires and cables. This product features a lengthwise slit, making it easy to install onto a bundle of cables or a pre-assembled harness assembly. Tubing is offered in various diameters and lengths to solve a broad range of harnessing or bundling needs.



- For use in enclosures or indoors only
- Abrasion resistant and provides light crush and impact resistance

Part Number	Material	Color	Length Per Reel*		Inside Diameter		Outside Diameter		Temperature Range	Std. Pkg. Qty.
			Ft.	m	In.	mm	In.	mm		
Slit Wall										
CLT25F-C20	Polyethylene	Black	100	30.5	0.28	7.2	0.40	10.1	-40°F – 122°F (-40°C – 50°C)	1
CLT50F-C20					0.51	13.0	0.65	16.6		
CLT75F-C20					0.77	19.5	0.94	23.9		
CLT100F-C20					0.91	23.2	1.10	28.0		
CLT125F-L20			50	15.2	1.28	32.5	1.54	39.0		

*Reel packaging may contain splices. Contact Panduit Customer Service for further information.


Duct Seal – Sealing Compounds

Duct Seal is safe and easy to use, non-corrosive, non-toxic, contains no asbestos, will not stain or harm hands and has no unpleasant odor. Perfect for sealing irregular openings off from air, dust, or water. The non-hardening sealant adheres to metal, masonry, wood, or plastic and provides excellent vibration damping.

- Dielectric strength: 200V/Mil, Min 0.030" thick
- 10 year minimum shelf life
- Temperature range: -30°F – 210°F (-34°C – 98°C)
- Indoor use only



Part Number	Part Description	Std. Pkg. Qty.
DS1	Duct seal (sealing compound) 1 lb. package	1



**Like what you see...
and want more?**

Visit www.panduit.com for the full offering of Panduit products