


TABLE 1 - FPONSS1X32

PART NUMBER	DESCRIPTION	LONG RIBBON QTY	NUMBER OF INPUTS	NUMBER OF OUTPUTS	SPLITTER ENCLOSURE DIMENSIONS		
					LENGTH (L)	WIDTH (W)	THICKNESS (T)
FPONSS1X32	FIBER OPTIC PLC SPLITTER 1 X 32 BARE FIBERS	4	1	32	1.97 [50]	0.28 [7]	0.16 [4]

- NOTES
- IDENTIFICATION:
PON PLC SPLITTER WITH BARE FIBERS
 - FIBER:
A. TYPE: 9/125um (SINGLEMODE)
B. JACKET DIAMETER: 900 MICRON
 - ALL PURCHASED ITEMS MUST CONFORM TO C2-0834 PANDUIT SPECIFICATION FOR CHEMICAL SUBSTANCES TO BE CONTROLLED IN PRODUCT AND PACKAGING.



PON SPLITTER ASSEMBLY DIAGRAM

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	02-21-20	SAT	SCAL	SKH	INITIAL RELEASE	00472ECH-DC

TITLE		FIBER OPTIC PLC SPLITTER WITH BARE FIBER		
ITEM REVISION NAME		00472ECH/00		
DATASET FILE NAME		00472ECH_DC/00A		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PART NUMBER		
.x ± .1 [2.54]	.xxx ± .005 [.127]	FPONSS1X32		
.xx ± .01 [.25]	ANGLES ± 1°	DRAWING NUMBER:		
THIRD ANGLE PROJECTION		00472ECH-DC		
DRAWN BY	DATE	CHK	SCALE	SIZE
SAT	02-10-20	SCAL	NONE	SHT 1 OF 1