


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- *1. REFER TO www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR
- 2. SPLICING MAY OCCUR FOR ROLL SIZES LONGER THAN 10 FT.
- 3. REVERSE CUT.
- 4. SOME GAP WILL BE PRESENT BETWEEN WINDS
- 5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS EUROPEAN DIRECTIVE ON THE RESTRICTION OF HAZARDOUS SUBSTANCES AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- 6. DIMENSIONS IN [] ARE METRIC.

*PANDUIT PART NUMBER	A IN [mm]	B IN [mm]	T IN [mm]	WEIGHT LBS (g)/ 100 FT
T12T	.125 [3.2]	.218 ±.047 [5.5 ±1.2]	.020 ±.006 [0.5 ±0.2]	0.6 (250)
T19T	.188 [4.8]	.250 ±.047 [6.4 ±1.2]	.030 ±.008 [0.8 ±0.2]	1.4 (650)
T25T	.250 [6.4]	.375 ±.047 [9.5 ±1.2]	.030 ±.008 [0.8 ±0.2]	2.0 (900)
T38T	.375 [9.5]	.437 ±.047 [11.1 ±1.2]	.030 ±.010 [0.8 ±0.3]	3.1 (1400)
T50T	.500 [12.7]	.500 ±.047 [12.7 ±1.2]	.030 ±.016 [0.8 ±0.4]	4.2 (1900)
T62T	.625 [15.9]	.625 ±.047 [15.9 ±1.2]	.030 ±.020 [0.8 ±0.5]	5.3 (2400)
T75T	.750 [19.1]	.875 ±.047 [22.2 ±1.2]	.030 ±.020 [0.8 ±0.5]	6.4 (2900)
T100T	1.000 [25.4]	1.125 ±.047 [28.6 ±1.2]	.040 ±.020 [1.0 ±0.5]	11.3 (5150)



PART NUMBER					SEE TABLE																			
TITLE										FLUOROPOLYMER SPIRAL WRAP														
CUSTOMER DRAWING																								
ITEM REVISION NAME					03903NBH/00																			
DATASET FILE NAME					03903NBH_DC/00A					PANDUIT														
MATERIAL					FLUOROPOLYMER																			
DRAWN BY					KLN					DRAWING NUMBER					03903NBH-DC									
DATE					06/19/2024					THIRD ANGLE PROJECTION					SHEET 1 OF 1									
CHK					MSAD					SCALE					NONE									
REV					00A					DESCRIPTION					ECN					GAECN07147/00				
BY					KLN					APR					DESCRIPTION					ECN				

A-SIZE CUSTOMER